


| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | AB1 | REVISED PER ECN-22-177079 | 29SEP2022 | RK  | MF   |

D



C

B


A



$0.64 \pm 0.02$  [.025  $\pm$  .001]  $\phi 0.38[.015]$  M TYP AT POST TIPS



RECOMMENDED HOLE LAYOUT



SECTION A-A

- $\triangle 1$  .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- $\triangle 2$  POINT OF MEASUREMENT FOR PLATING THICKNESS.
- $\triangle 3$  THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- $\triangle 4$  ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- $\triangle 5$  .000100 BRIGHT TIN OVER .000050 NICKEL.
- $\triangle 6$  PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- $\triangle 7$  .000100 MATTE TIN OVER .000050 NICKEL.
- $\triangle 8$  HIGH TEMPERATURE CONFIGURATION
- $\triangle 9$  STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- $\triangle 10$  SUPERSEDED BY P/N 5-103639-2.
- $\triangle 11$  OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- $\triangle 12$  0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

D

C

B

A

|                                        |  |                               |                                                                                          |                 |                        |
|----------------------------------------|--|-------------------------------|------------------------------------------------------------------------------------------|-----------------|------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>S.SHUEY<br>05MAR91     | TE Connectivity                                                                          |                 |                        |
| DIMENSIONS:<br>mm [INCHES]             |  | CHK<br>L.CASTAGNA<br>27MAR93  |                                                                                          |                 |                        |
|                                        |  | APVD<br>L.CASTAGNA<br>27MAR93 | NAME                                                                                     |                 |                        |
|                                        |  | PRODUCT SPEC<br>108-25034     | HDR ASY,VERT,SNGL ROW<br>2.54[100] C/L 0.64[025] SQ PST,<br>WITH PLZN&LTCHNG,AMPMODU MTE |                 |                        |
| MATERIAL                               |  | APPLICATION SPEC<br>114-25026 | SIZE<br>A2                                                                               | CAGE CODE<br>-  | DRAWING NO<br>C=103639 |
| HOUSING:                               |  | WEIGHT<br>-                   | RESTRICTED TO<br>-                                                                       |                 |                        |
|                                        |  | FINISH<br>SEE TABLE           | CUSTOMER DRAWING                                                                         |                 |                        |
|                                        |  |                               | SCALE<br>4:1                                                                             | SHEET<br>1 OF 2 | REV<br>AB1             |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103639-4](#)