


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AB1	REVISED PER ECN-22-177079	29SEP2022	RK	MF

D

C


B

A



0.64±0.02  
[.025±.001]


0.38 [.015] M  
TYP AT POST TIPS




1.52±0.08  
[.060±.003]

3.05<sup>+0.13</sup><sub>-0.18</sub>  
[.120<sup>+0.005</sup><sub>-.007</sub>]

1.52±0.08  
[.060±.003]



RECOMMENDED HOLE LAYOUT



0.64±0.05  
[.025±.002]

6.98<sup>+0.43</sup><sub>-0.30</sub>  
[.275<sup>+0.017</sup><sub>-.012</sub>]

- 1 .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 .000100 BRIGHT TIN OVER .000050 NICKEL.
- 6 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 7 .000100 MATTE TIN OVER .000050 NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION
- 9 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- 10 SUPERSEDED BY P/N 5-103639-2.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 12 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

SECTION A-A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY 05MAR91	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK L.CASTAGNA 27MAR93			
		APVD L.CASTAGNA 27MAR93	NAME HDR ASY,VERT,SNGL ROW 2.54[100] C/L 0.64[025] SQ PST, WITH PLZN&LTCHNG,AMPMODU MTE		
		PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026	SIZE A2		
MATERIAL HOUSING:		FINISH SEE TABLE	WEIGHT -	CAGE CODE -	DRAWING NO 103639
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 2	REV AB1



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103639-1](#)