


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AB1	REVISED PER ECN-22-177079	29SEP2022	RK	MF

D



C

B


A



0.64 ± 0.02 [.025 \pm .001] $\phi 0.38[.015]$ M TYP AT POST TIPS



RECOMMENDED HOLE LAYOUT



SECTION A-A

- $\triangle 1$.000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- $\triangle 2$ POINT OF MEASUREMENT FOR PLATING THICKNESS.
- $\triangle 3$ THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- $\triangle 4$ ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- $\triangle 5$.000100 BRIGHT TIN OVER .000050 NICKEL.
- $\triangle 6$ PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- $\triangle 7$.000100 MATTE TIN OVER .000050 NICKEL.
- $\triangle 8$ HIGH TEMPERATURE CONFIGURATION
- $\triangle 9$ STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- $\triangle 10$ SUPERSEDED BY P/N 5-103639-2.
- $\triangle 11$ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- $\triangle 12$ 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY 05MAR91	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK L.CASTAGNA 27MAR93			
		APVD L.CASTAGNA 27MAR93	NAME		
		PRODUCT SPEC 108-25034	HDR ASY,VERT,SNGL ROW 2.54[100] C/L 0.64[025] SQ PST, WITH PLZN<CHNG,AMPMODU MTE		
MATERIAL		APPLICATION SPEC 114-25026	SIZE A2	CAGE CODE -	DRAWING NO C=103639
HOUSING:		WEIGHT -	RESTRICTED TO -		
		FINISH SEE TABLE	CUSTOMER DRAWING		
			SCALE 4:1	SHEET 1 OF 2	REV AB1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103639-3](#)