



























































































































| | | |
|------------------------------|--------------------------|----------------------|
| THIS DRAWING IS UNPUBLISHED. | RELEASED FOR PUBLICATION | 103639, 103639 |
| © COPYRIGHT 103639y - | | ALL RIGHTS RESERVED. |

| REVISIONS | | | | | |
|-----------|-----|-------------|------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | — | SEE SHEET 1 | — | — | — |

| | | | | | | | | |
|---|---|------------------|------------------|----|-------------------|------------|----------|---|
|  |  | 64.01 [2.520] | 65.91 [2.595] | 24 | 25 | 7-103639-4 | OBSOLETE |  |
|  |  | 61.47 [2.420] | 63.37 [2.495] | 23 | 24 | 7-103639-3 | OBSOLETE |  |
|  |  | 58.93 [2.320] | 60.83 [2.395] | 22 | 23 | 7-103639-2 | OBSOLETE |  |
|  |  | 56.39 [2.220] | 58.29 [2.295] | 21 | 22 | 7-103639-1 | | |
|  |  | 53.85 [2.120] | 55.75 [2.195] | 20 | 21 | 7-103639-0 | OBSOLETE |  |
|  |  | 51.31 [2.020] | 53.21 [2.095] | 19 | 20 | 6-103639-9 | | |
|  |  | 48.77 [1.920] | 50.67 [1.995] | 18 | 19 | 6-103639-8 | OBSOLETE |  |
|  |  | 46.23 [1.820] | 48.13 [1.895] | 17 | 18 | 6-103639-7 | OBSOLETE |  |
|  |  | 43.69 [1.720] | 45.59 [1.795] | 16 | 17 | 6-103639-6 | | |
|  |  | 41.15 [1.620] | 43.05 [1.695] | 15 | 16 | 6-103639-5 | | |
|  |  | 38.61 [1.520] | 40.51 [1.595] | 14 | 15 | 6-103639-4 | | |
|  |  | 36.07 [1.420] | 37.97 [1.495] | 13 | 14 | 6-103639-3 | | |
|  |  | 33.53 [1.320] | 35.43 [1.395] | 12 | 13 | 6-103639-2 | | |
|  |  | 30.99 [1.220] | 32.89 [1.295] | 11 | 12 | 6-103639-1 | | |
|  |  | 28.45 [1.120] | 30.35 [1.195] | 10 | 11 | 6-103639-0 | | |
|  |  | 25.91 [1.020] | 27.81 [1.095] | 9 | 10 | 5-103639-9 | | |
|  |  | 23.37 [.920] | 25.27 [0.995] | 8 | 9 | 5-103639-8 | | |
|  |  | 20.83 [.820] | 22.73 [.895] | 7 | 8 | 5-103639-7 | | |
|  |  | 18.29 [.720] | 20.19 [.795] | 6 | 7 | 5-103639-6 | | |
|  |  | 15.75 [.620] | 17.65 [.695] | 5 | 6 | 5-103639-5 | | |
|  |  | 13.21 [.520] | 15.11 [.595] | 4 | 5 | 5-103639-4 | | |
|  |  | 10.67 [.420] | 12.57 [.495] | 3 | 4 | 5-103639-3 | | |
|  |  | 8.13 [.320] | 10.03 [.395] | 2 | 3 | 5-103639-2 | | |
|  |  | 5.59 [.220] | 7.49 [.295] | 1 | 2 | 5-103639-1 | | |
| REMARKS | PLATING | C | B | A | NO. OF POSN | PART NO. | | |

| | | | | | | | |
|-----|---|---|---|------------------|------------------|-----|-------------------|
| △10 |  |  | 15.75 [.620] | 17.65 [.695] | 5 | 6 | 3-103639-3 |
| |  |  | 10.67 [.420] | 12.57 [.495] | 3 | 4 | 3-103639-2 |
| |  |  | 8.13 [.320] | 10.03 [.395] | 2 | 3 | 3-103639-1 |
| |  |  | 30.99 [1.220] | 32.89 [1.295] | 1 1 | 12 | 3-103639-0 |
| |  |  | 25.91 [1.020] | 27.81 [1.095] | 9 | 10 | 2-103639-9 |
| |  |  | 20.83 [.820] | 22.73 [.895] | 7 | 8 | 2-103639-8 |
| △6 |  |  | 18.29 [.720] | 20.19 [.795] | 6 | 7 | 2-103639-7 |
| |  |  | 13.21 [.520] | 15.11 [.595] | 4 | 5 | 2-103639-6 |
| |  |  | 5.59 [.220] | 7.49 [.295] | 1 | 2 | 2-103639-5 |
| TE |  |  | 64.01 [2.520] | 65.91 [2.595] | 24 | 25 | 2-103639-4 |
| TE |  |  | 61.47 [2.420] | 63.37 [2.495] | 23 | 24 | 2-103639-3 |
| TE |  |  | 58.93 [2.320] | 60.83 [2.395] | 22 | 23 | 2-103639-2 |
| -1 |  |  | 56.39 [2.220] | 58.29 [2.295] | 2 1 | 22 | 2-103639-1 |
| TE |  |  | 53.85 [2.120] | 55.75 [2.195] | 20 | 2 1 | 2-103639-0 |
| |  |  | 51.31 [2.020] | 53.21 [2.095] | 19 | 20 | 1-103639-9 |
| |  |  | 48.77 [1.920] | 50.67 [1.995] | 18 | 19 | 1-103639-8 |
| |  |  | 46.23 [1.820] | 48.13 [1.895] | 17 | 18 | 1-103639-7 |
| |  |  | 43.69 [1.720] | 45.59 [1.795] | 16 | 17 | 1-103639-6 |
| |  |  | 41.15 [1.620] | 43.05 [1.695] | 15 | 16 | 1-103639-5 |
| |  |  | 38.61 [1.520] | 40.51 [1.595] | 14 | 15 | 1-103639-4 |
| |  |  | 36.07 [1.420] | 37.97 [1.495] | 13 | 14 | 1-103639-3 |
| |  |  | 33.53 [1.320] | 35.43 [1.395] | 12 | 13 | 1-103639-2 |
| |  |  | 30.99 [1.220] | 32.89 [1.295] | 1 1 | 12 | 1-103639-1 |
| | -0 |  |  | 28.45 [1.120] | 30.35 [1.195] | 10 | 1 1 |
| |  |  | 25.91 [1.020] | 27.81 [1.095] | 9 | 10 | 103639-9 |
| |  |  | 23.37 [.920] | 25.27 [0.995] | 8 | 9 | 103639-8 |
| |  |  | 20.83 [.820] | 22.73 [.895] | 7 | 8 | 103639-7 |
| |  |  | 18.29 [.720] | 20.19 [.795] | 6 | 7 | 103639-6 |
| |  |  | 15.75 [.620] | 17.65 [.695] | 5 | 6 | 103639-5 |
| |  |  | 13.21 [.520] | 15.11 [.595] | 4 | 5 | 103639-4 |
| |  |  | 10.67 [.420] | 12.57 [.495] | 3 | 4 | 103639-3 |
| |  |  | 8.13 [.320] | 10.03 [.395] | 2 | 3 | 103639-2 |
| |  |  | 5.59 [.220] | 7.49 [.295] | 1 | 2 | 103639-1 |
| | REMARKS | | PLATING | C | B | A | NO. OF POSN |

| | | | | | |
|---|--|---|--|---|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN 05MAR91 S.SHUEY CHK 27MAR93 L.CASTAGNA APVD 27MAR93 L.CASTAGNA PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026 | |  TE Connectivity | |
| DIMENSIONS: mm [INCHES] | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | NAME HDR ASY,VERT,SNGL ROW 2.54[.100]C/L 0.64[.025]SQ PST, WTH PLZN<CHNG,AMPMODU MTE | |
|  | | 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± - | | | |
| MATERIAL | | FINISH | | | |
| HOUSING: SEE TABLE | | WEIGHT - | | SIZE A2 CAGE CODE - DRAWING NO C-103639 RESTRICTED TO - | |
| CUSTOMER DRAWING | | SCALE 1:1 | | SHEET 2 of 2 REV AB1 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103639-4](#)