

8

7

6

5

4

3

2

1

TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

8 8	9	7	41.15 [1.620]	43.05 [1.695]	15	16	2-103673-6
		7	18.29 [.720]	20.19 [.795]	6	7	2-103673-5
		1	64.01 [2.520]	65.91 [2.595]	24	25	2-103673-4
		1	61.47 [2.420]	63.37 [2.495]	23	24	2-103673-3
		1	58.93 [2.320]	60.83 [2.395]	22	23	2-103673-2
		1	56.39 [2.220]	58.29 [2.295]	21	22	2-103673-1
		1	53.85 [2.120]	55.75 [2.195]	20	21	2-103673-0
		1	51.31 [2.020]	53.21 [2.095]	19	20	1-103673-9
		1	48.77 [1.920]	50.67 [1.995]	18	19	1-103673-8
		1	46.23 [1.820]	48.13 [1.895]	17	18	1-103673-7
		1	43.69 [1.720]	45.59 [1.795]	16	17	1-103673-6
		1	41.15 [1.620]	43.05 [1.695]	15	16	1-103673-5
		1	38.61 [1.520]	40.51 [1.595]	14	15	1-103673-4
		1	36.07 [1.420]	37.97 [1.495]	13	14	1-103673-3
		1	33.53 [1.320]	35.43 [1.395]	12	13	1-103673-2
		1	30.99 [1.220]	32.89 [1.295]	11	12	1-103673-1
		1	28.45 [1.120]	30.35 [1.195]	10	11	1-103673-0
		1	25.91 [1.020]	27.81 [1.095]	9	10	103673-9
		1	23.37 [.920]	25.27 [0.995]	8	9	103673-8
		1	20.83 [.820]	22.73 [.895]	7	8	103673-7
1	18.29 [.720]	20.19 [.795]	6	7	103673-6		
1	15.75 [.620]	17.65 [.695]	5	6	103673-5		
1	13.21 [.520]	15.11 [.595]	4	5	103673-4		
1	10.67 [.420]	12.57 [.495]	3	4	103673-3		
1	8.13 [.320]	10.03 [.395]	2	3	103673-2		
1	5.59 [.220]	7.49 [.295]	1	2	103673-1		
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.	

REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.
---------	---------	---	---	---	-------------------	----------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0. PLC ± - 1. PLC ± - 2. PLC ± 0.13[.005] 3. PLC ± - 4. PLC ± - ANGLES FINISH SEE TABLE

MATERIAL: HOUSING: FLAME RETARDENT LCP COLOR: BLACK CONTACTS: BRASS	WEIGHT
--	--------

DWN S. SHUEY	OSMAR91
CHK J. GESFORD	OSMAR91
APVD J. GESFORD	OSMAR91
NAME	
PRODUCT SPEC	
APPLICATION SPEC	
SIZE	
CAGE CODE	
DRAWING NO	
SCALE	
SHEET	
REV	

108-25034	114-25026
-----------	-----------

100779	103673
--------	--------

CUSTOMER DRAWING	SCALE 4:1	SHEET 2 OF 2	REV W1
------------------	-----------	--------------	--------

TE Connectivity Ltd.

HDR ASSY, RTANG, SINGLE ROW
2.54[.100] C/L 0.641[.025] SQ. POST,
WITH PLZN & HOLD DOWNS, AMPMODU MTE

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103673-4](#)