




1. FINISH: .00038[.000015] GOLD IN THE CONTACT AREA, .00254[.000100] MATTE TIN-LEAD ON REMAINDER OF CONTACT, ALL OVER .00127[.000050] NICKEL.
2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
3. THE NOTED DIMENSIONS APPLY FROM THE BASIC DIMENSION CENTER LINE (NOT THE POST CENTER LINE) TO THE SURFACE INDICATED.
4. ONE POLARIZATION SLOT FOR 2 AND 3 POSITION ASSEMBLIES ONLY.
5. SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD DOWN UNTIL SOLDERED, CONFIGURATION ACCEPTS 0.69[.027]-2.03[.080] THICK PRINTED CIRCUIT BOARD. (SEE DETAIL Z).
6. PARTS ARE PACKAGED IN GANG OF TUBES.
7. DIMENSIONS NOTED ARE FOR SOLDER STENCIL LAYOUT FOR USE WITH 1.58±0.20[.062±.008] THICK PRINTED CIRCUIT BOARDS.
8. MATERIAL- HOUSING: LCP, COLOR-BLACK.
POSTS: BRASS.
9. FINISH: .00038[.000015] GOLD IN THE CONTACT AREA, .00254[.000100] MATTE TIN ON REMAINDER OF CONTACT, ALL OVER .00127[.000050] NICKEL.
10. 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

	32.89 [1.295]	30.99 [1.220]	1 1	12	6-104809-
	30.35 [1.195]	28.45 [1.120]	10	1 1	6-104809-
	27.81 [1.095]	25.91 [1.020]	9	10	5-104809-
	25.27 [.995]	23.37 [.920]	8	9	5-104809-
	22.73 [.895]	20.83 [.820]	7	8	5-104809-
	20.19 [.795]	18.29 [.720]	6	7	5-104809-
	17.65 [.695]	15.75 [.620]	5	6	5-104809-
	15.11 [.595]	13.21 [.520]	4	5	5-104809-
	12.57 [.495]	10.67 [.420]	3	4	5-104809-
	10.03 [.395]	8.13 [.320]	2	3	5-104809-
	7.49 [.295]	5.59 [.220]	1	2	5-104809-
	32.89 [1.295]	30.99 [1.220]	1 1	12	1-104809-
	30.35 [1.195]	28.45 [1.120]	10	1 1	1-104809-
	27.81 [1.095]	25.91 [1.020]	9	10	104809-
	25.27 [.995]	23.37 [.920]	8	9	104809-
	22.73 [.895]	20.83 [.820]	7	8	104809-
	20.19 [.795]	18.29 [.720]	6	7	104809-
	17.65 [.695]	15.75 [.620]	5	6	104809-
	15.11 [.595]	13.21 [.520]	4	5	104809-
	12.57 [.495]	10.67 [.420]	3	4	104809-
	10.03 [.395]	8.13 [.320]	2	3	104809-
	7.49 [.295]	5.59 [.220]	1	2	104809-
PLATING	C	B	A	NO. OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	09F01	 TE Connectivity	
		CHK K WRIGHT	09F01		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: APVD K WRIGHT		NAME	
		PRODUCT SPEC — APPLICATION SPEC —		PLZD HDR ASSY, AMPMODU MTE, VERTICAL SINGLE ROW, 2.54[.100] CL, 0.64[.025] SQ POSTS, WITH LATCHING & HOLD DOWN	
MATERIAL SEE NOTE 8		FINISH SEE TABLE		SIZE A1	
		WEIGHT 0.000000		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO 104809	
				RESTRICTED TO —	
				SCALE 4:1	
				SHEET 1 of 1	
				REV P	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-104809-9](#)