





2		1					
LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			F1	REVISED PER PCN E-17-014802	06OCT2017	AJ	DM
			G	REVISED PER PCN E-20-008101	12JUN2020	DM	DM
			G1	REVISED PER PCN-22-157823	12OCT2022	SP	DM



SECTION A-A
WIRE BARRELL



SECTION B-B
INSULATION BARREL

5 TIN PLATING MAY BE IN THIS REGION.

4 TIN PLATED REGION.


3 MATERIAL:
BODY: .012 [0.30] THICK COPPER ALLOY
SLEEVE: STAINLESS STEEL

2. WIRE RANGE: 20 AWG TO 16 AWG [0.5-1.0 mm²]
INSULATION RANGE: Ø.055-.100 [Ø1.40-2.54]

1 44: GOLD PLATED REGION.
88: PALLADIUM-NICKEL PLATED REGION.

NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PN	DEUTSCH PN	PLATING
1062-16-0622	1062-16-0622	Ni/Cu overall, Sn/Ni/Cu Wire Barrel
1062-16-0644	1062-16-0644	Selective Au, Ni/Cu overall, Sn/Ni/Cu Wire Barrel
1062-16-0677	1062-16-0677	Sn/Ni/Cu overall
1062-16-0688	1062-16-0688	Selective Pd-Ni, Au/Ni/Cu overall

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN STEVE PALLUTH 28NOV2000	 TE Connectivity						
		CHK VLADIMIR TOMSA 06DEC2000							
DIMENSIONS: INCHES[mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. REED 08DEC2000	NAME SOCKET, STAMPED AND FORMED SIZE 16 16-20AWG						
	0 PLC ±	PRODUCT SPEC	SIZE A3				CAGE CODE 4AFU8	DRAWING NO C-1062-16-06XX	RESTRICTED TO -
	1 PLC ±	108-151000							
	2 PLC ±	APPLICATION SPEC							
	3 PLC ±0.025 [0.64]	114-151000							
	4 PLC ±	WEIGHT 0.42 g							
	ANGLES ±								
MATERIAL 	FINISH SEE TABLE								
Customer Drawing			SCALE 6:1		SHEET 1 OF 1		REV G1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1062-16-0644](#)