



P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA5	REVISED PER ECR-22-129998	12APR2022	WH	LC

- 1 MATING CONN P/N: □-1123722-□
- 2 APPLICABLE P.C.B LAYOUT: SEE FIG. 1
- 3 APPLICABLE P.C.B THICKNESS: 1.60
- 4 SKETCHES SHOW NO PINS MISSING.
- 6 PIN: POST TIN OVER BRASS
- 7 HOUSING: PBT, 30% GLASS, UL94-V0(ONLY NATURAL COLOR).
- 8 ○ : WITH PIN,
X : WITHOUT PIN.
- 10 SUPERSEDED BY 1744489-2.
- 11 SUPERSEDED BY 1744489-4.
- 12 SUPERSEDED BY 1744489-5.
- 13 SUPERSEDED BY 1744489-6.
- 14 SUPERSEDED BY 1744489-7.
- 15 SUPERSEDED BY 1744489-8.
- 16 SUPERSEDED BY 1744489-9.
- 17 SUPERSEDED BY 1-1744489-0.
- 18 SUPERSEDED BY 1-1744489-1.
- 19 VALUES FOR UL 61800-5-1, ONLY NATURAL COLOR.

Flam	RTIe deg C	HWI	HAI	CTI
V0	130	PLC 2	PLC 4	PLC 2_UL746


- 20 PRELIMINARY: NOT FOR PRODUCTION



2 FIG.1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01	TE Connectivity		
DIMENSIONS: mm		CHK M.SHINDO 13MAR'01			
		APVD Y.KASHIWA 13MAR'01	NAME		
		PRODUCT SPEC 108-5609	3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY		
MATERIAL SEE TABLE		APPLICATION SPEC 114-32134	SIZE A2	CAGE CODE 00779	DRAWING NO C=1123723
FINISH SEE TABLE		WEIGHT -	RESTRICTED TO -		REV AA5
CUSTOMER DRAWING			SCALE N/A	SHEET 1 OF 2	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



8-1123723-3 SHOW

○	○	○	○	○	○	○	○	○	○	○	○	39.60	41.00	43.50	NATURAL	11	18	8-1123723-1
○	○	○	○	○	○	○	○	○	○	○	○				GREEN		6-1123723-1	
○	○	○	○	○	○	○	○	○	○	○	○				BLACK		5-1123723-1	
○	○	○	○	○	○	○	○	○	○	○	○				RED		4-1123723-1	
○	○	○	○	○	○	○	○	○	○	○	○				BLUE		3-1123723-1	
○	○	○	○	○	○	○	○	○	○	○	○				YELLOW		2-1123723-1	
○	○	○	○	○	○	○	○	○	○	○	○				NATURAL		1-1123723-1	
○	○	○	○	○	○	○	○	○	○	△	35.64	37.04	39.54	NATURAL	10	17	7-1123723-0	
○	○	○	○	○	○	○	○	○	○	△				GREEN		6-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				BLACK		5-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				RED		4-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				BLUE		3-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				YELLOW		2-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				NATURAL		1-1123723-0		
○	○	○	○	○	○	○	○	○	○	△	31.68	33.08	35.58	NATURAL	16	7	7-1123723-9	
○	X	○	○	○	X	○	○	○	○	○	39.60	41.00	43.50	NATURAL		7	7-1123723-1	
○	○	○	○	○	○	○	○	○	○	△	31.68	33.08	35.58	GREEN		9	6	6-1123723-9
○	○	○	○	○	○	○	○	○	○	△				BLACK			5	5-1123723-9
○	○	○	○	○	○	○	○	○	○	△				RED			4	4-1123723-9
○	○	○	○	○	○	○	○	○	○	△				BLUE			3	3-1123723-9
○	○	○	○	○	○	○	○	○	○	△				YELLOW			2	2-1123723-9
○	○	○	○	○	○	○	○	○	○	△				NATURAL	1		1-1123723-9	
○	○	○	○	○	○	○	○	○	○	△								
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"	REF	"A"	REF	COLOR	POS	ASS'Y P/N
PIN POSITION											DIMENSION							

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01 CHK M.SHINDO 13MAR'01		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD Y.KASHIWA 13MAR'01		3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY	
		PRODUCT SPEC 108-5609			
		APPLICATION SPEC 114-32134			
		WEIGHT -			
0 PLC ± 1 PLC ± 0.50 2 PLC ± 0.30 3 PLC ± 4 PLC ± ANGLES ± 3°		SIZE		CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
SEE TABLE		SEE TABLE		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE N/A	
				SHEET 2 of 2	
				REV AA5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1123723-0](#)