

8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
3. COPYRIGHT 20		BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.	
PART NUMBER	REVISION	DESCRIPTION	FEED TYPE
2151205-1	G	FINE CRIMP HEIGHT ADJUST	MECHANICAL
2151205-2	H	FINE CRIMP HEIGHT ADJUST	PNEUMATIC
5-2151205-1	G	SEAL STRIPPER CRIMPER TERMINATING UNIT	MECHANICAL
5-2151205-2	H	SEAL STRIPPER CRIMPER TERMINATING UNIT	PNEUMATIC
7-2151205-1	G	MECHANICAL AND CRIMP TOOLING KIT	MECHANICAL
7-2151205-2	H	PNEUMATIC AND CRIMP TOOLING KIT	PNEUMATIC
7-2151205-7	A	CRIMP TOOLING KIT	-


APPLICATOR DATA		
CRIMP	SIZE	TYPE
WIRE	2.28 mm [.090]	F
INSUL	3.68 mm [.145]	O
APPLICATOR INSTRUCTIONS 408-35042		

TERMINAL DATA: TE TERMINAL		TE CRIMP SPECIFICATION	
TERMINAL NAME: MINI MIC RECEPT CONTACT			
WIRE STRIP LENGTH 3.00-3.50 mm [.118-.138 IN]		INSULATION DIAMETER RANGE Ø1.70-3.30 mm [.067-.130 IN]	
TERMINAL APPLICATION SPECIFICATION		(A)114-20045	-
		(B)114-20062	-


TERMINALS APPLIED				SEAL INSULATION DIAMETER RANGE
TE TERMINAL	TE TERMINAL	TE SEAL	TE SEAL	
(A) 282110-1			(A) 281934-2	Ø1.7-2.4mm
			(A) 281934-3	Ø2.5-3.3mm
			(B) 828904-1	Ø1.9-2.1mm
			(B) 82890	

LOC		DIST		REVISIONS			
A	66	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-


FEED TYPE MECHANICAL



PNEUMATIC





FEED SPRING SETTING POSITION
(SHOWN FROM REAR SIDE)



DETAIL A

CAM POSITIONS



8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
20		20	
COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.			
PART NUMBER	REVISION	DESCRIPTION	FEED TYPE
2-2151205-1	G	FINE CRIMP HEIGHT ADJUST	MECHANICAL
2-2151205-2	H	FINE CRIMP HEIGHT ADJUST	PNEUMATIC
7-2151205-7	A	CRIMP TOOLING KIT	-

PACIFIC VERSION TERMINATOR
INTERFACE ADAPTER



APPLICATOR DATA		
CRIMP	SIZE	TYPE
WIRE	2.28 mm [.090]	F
INSUL	3.68 mm [.145]	O
APPLICATOR INSTRUCTIONS 408-35042		

TERMINAL DATA: TE TERMINAL		TE CRIMP SPECIFICATION	
TERMINAL NAME: MINI MIC RECEPT CONTACT			
WIRE STRIP LENGTH 3.00-3.50 mm [.118-.138 IN]		INSULATION DIAMETER RANGE Ø1.70-3.30 mm [.067-.130 IN]	
TERMINAL APPLICATION SPECIFICATION	(A)114-20045	-	-
	(B)114-20062	-	-

TERMINALS APPLIED				SEAL INSULATION DIAMETER RANGE
TE TERMINAL	TE TERMINAL	TE SEAL	TE SEAL	
(A) 282110-1			(A) 281934-2	Ø1.7-2.4mm
			(A) 281934-3	Ø2.5-3.3mm
			(B) 828904-1	Ø1.9-2.1mm
			(B) 828905-1	Ø2.2-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2151205-1](#)