


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B6	REVISED PER ECN-23-225679	08AUG2023	WLS	VS
	B7	REVISED PER ECN-23-242776	14DEC2023	WLS	VS



-HOUSING

2 RECOMMENDED PC BOARD THICKNESS OF 1.57.


RETENTION BUMP FEATURES FACE EACH OTHER, TYPICAL ALL CONFIGURATIONS.

4 PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING AREA.
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS.
ALL OVER 1.27 μ m MINIMUM NICKEL.

5 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACCORDING TO NUMBER OF POSITION).


6 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

 CUTTING EDGE, NO PLATING PRESENT IN THE REGION SHOWN.



OBSOLETE	1, 2, 11, 12	33.00	39.14	37.00	12	3-1445084-2
OBSOLETE	1, 2, 9, 10	30.00	36.14	34.00	11	3-1445084-1
OBSOLETE	1, 2, 9, 10	27.00	33.14	31.00	10	3-1445084-0
OBSOLETE	1, 2, 7, 8	24.00	30.14	28.00	9	2-1445084-9
	1, 2, 7, 8	21.00	27.14	25.00	8	2-1445084-8
OBSOLETE	1, 2, 5, 6	18.00	24.14	22.00	7	2-1445084-7
OBSOLETE	1, 2, 5, 6	15.00	21.14	19.00	6	2-1445084-6
OBSOLETE	1, 2, 3, 4	12.00	18.14	16.00	5	2-1445084-5
	1, 2, 3, 4	9.00	15.14	13.00	4	2-1445084-4
	1, 2	6.00	12.14	10.00	3	2-1445084-3
	1, 2	3.00	9.14	7.00	2	2-1445084-2
	CON POS W/RET BUMP 	DIM Z	DIM V	DIM L	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 100CT2000 CHK J. ROOT 17-APR-2001 K. WHITAKER APVD C. JONES 17-APR-2001		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.20 3 PLC ±. 4 PLC ±. ANGLES ±° MATERIAL FINISH		NAME VERTICAL THRU HOLE HEADER ASSY, 0.38 MIC GOLD CONTACTS W/PCB PLZN™ FEATURE, SGL ROW, MICRO MATE-N-LOK™	
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-1445084	
				RESTRICTED TO -	
				SCALE 4:1 SHEET 1 OF 2 REV B7	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1445084-1](#)