


8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
2012		2012	
© COPYRIGHT 2012 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.			
PART NUMBER	REVISION	DESCRIPTION	FEED TYPE
2151698-2	F	FINE CRIMP HEIGHT ADJUST	PNEUMATIC
7-2151698-2	F	PNEUMATIC AND CRIMP TOOLING KIT	PNEUMATIC
7-2151698-7	A	CRIMP TOOLING KIT	-

APPLICATOR DATA		
CRIMP	SIZE	TYPE
WIRE	.176 [4.47 mm]	Ø
INSUL	-	-
APPLICATOR INSTRUCTIONS 408-35042		

TERMINAL DATA: TE TERMINAL		TE CRIMP SPECIFICATION	
TERMINAL NAME: FULLY INSULATED FASTON			
WIRE STRIP LENGTH .265-.297 IN [6.73-7.54 mm]			INSULATION DIAMETER RANGE 
TERMINAL APPLICATION SPECIFICATION	 114-2123	-	-
TERMINALS APPLIED 			
TE TERMINAL	TE TERMINAL	TE TERMINAL	TE TERMINAL
2-520080-2	9-520272-2	2-520306-2	
2-520083-2	2-521010-2	2-520310-2	
2-520272-2			


GROUP 1		GROUP 2	
WIRE SIZE	CRIMP HEIGHT INCH [mm]	CRIMP HEIGHT REFERENCE SETTING	Ø SOLDER
18	0.070+/-0.002 [1.78+/-0.05]	6.3	.12 IN [3.05mm]
20 or 22	0.065+/-0.002 [1.65+/-0.05]	7.7	.12 IN [3.05mm]



1. RECOMMENDED SPARE PARTS
2. REFER TO SUPPLIED INSTRUCTION SHEET FOR CLEANING, LUBRICATION AND STORAGE OF APPLICATOR.
3. CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.
4. ITEM 7 MUST BE REMOVED IF APPLICATOR IS USED ON BENCH MACHINE.
5. ITEMS 5 AND 9 OR ITEMS 10 AND 22 ARE REQUIRED WHEN RUNNING ON A LEADMAKER.
ITEM 42 OR 43 REQUIRED WHEN RUNNING ON A BENCH MACHINE.
6. FEED ADJUSTMENT MAY BE REQUIRED WHEN SWITCHING TERMINALS.
7. GROUP 1 TERMINALS: Ø.120 IN [3.05mm] MAX INSULATION
GROUP 2 TERMINALS: Ø.200 IN [5.08mm] MAX INSULATION
8. USE ITEMS 5, 9, OR 42 WITH GROUP 1 TERMINALS
USE ITEMS 10, 22, OR 43 WITH GROUP 2 TERMINALS
9. TO CHECK CRIMP HEIGHT. CRIMP SOLDER (Ø.12 IN [3.05mm] 60/40 SOLID CORE) AND MEASURE AT CENTER OF SLUG.
10. IT MAY BE NECESSARY TO MODIFY THE T-TERMINATING/K-PRESS BASE PLATE BEFORE USE BY ADDING A 10-32 HOLE TO RELOCATE THE FORWARD STOP AS SHOWN.
11. ITEMS 253 AND 255 MUST BE INSTALLED IN THE G-TERMINATING UNIT CHIP RELIEF HOLE BEFORE INSTALLING THE APPLICATOR.
12. ITEM 257, REQUIRED IF APPLICATOR IS RUN ON T-TERMINATING UNIT/K-PRESS. GUARD, ITEM 256, REQUIRED IF APPLICATOR IS BEING USED ON G-TERMINATOR.
13. TERMINAL PITCH NOT COMPATIBLE WITH MECHANICAL FEED.

14. UNLESS SPECIFIED OTHERWISE TORQUE VALUES SHALL BE USED PER DOCUMENT, 101-35000.

ATLANTIC VERSION TERMINATOR
INTERFACE ADAPTER



*WARNING
ON INSTALLATION, SET WIRE DISC TO CRIMP HEIGHT REFERENCE SETTING FOR LARGEST WIRE SIZE. CRIMP HEIGHT REFERENCE SETTINGS GREATER THAN THE VALUE SHOWN MAY CAUSE DAMAGE TO THE CRIMP TOOLING, REFER TO THE INSTRUCTION SHEET FOR PROPER SETUP AND ADJUSTMENTS.

ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)

LOC		DIST		REVISIONS			
A	66	P	LTR	DESCRIPTION	DATE	DWN	APVD
		C		ECR-18-017653	19NOV2018	JAH	CT
		D		ECR-18-019699	17DEC2018	JAH	CT
		E		ECR-19-009212	12JUN2019	FJ	TE
		F		ECR-19-014579	18SEP2019	FZ	TE

2	-	REF	REF	462992-7	GUARD ASSEMBLY	257
	-	REF	REF	679532-1	INSERT, GUARD	256
1	-	1	1	189728-1	BRACKET, SPACER	255
	-	1	1	568681-1	SPACER, BASE PLATE	253
1	-	1	1	2119641-1	FEED CAM, AIR FEED	248
	-	1	1	7-18023-7	SCR, SKT HD CAP M3 X 4.0	241
1	-	1	1	2844940-2	AIR FEED MODULE	238
	-	1	1	1-18028-0	WASHER, FLAT, REG M8	192
1	-	REF	REF	994970-2	COUNTER, MAGNETIC	164
	-	1	1	1-22281-8	SPRING, COMPRESSION	121
1	-	1	1	1-18028-2	WASHER, FLAT, REG M4	119
	-	1	1	2844908-1	SCREW, LOCKING	99
1	-	1	1	2844907-1	POST, LOCKING	98
	-	1	1	1-690438-0	FRONT STRIP GUIDE	96
1	-	2	2	2168083-1	SCR, SKT HD CAP, RoHS, M3 X 8.0	95
	-	4	4	18023-4	SCR, SKT HD CAP M3 X 10.0	94
1	-	1	1	2168083-6	SCR, SKT HD CAP, RoHS, M5 X 65	93
	-	1	1	455888-4	SPACER, CRIMPER	82
1	-	1	1	240641-9	SPACER	81
	-	1	1	1803607-3	DOCUMENTATION PACKAGE	71
1	-	1	1	2161332-2	DEPRESSOR, WIRE FUNNEL	70
	-	1	1	2161331-1	SPACER, WIRE FUNNEL DEPRESSOR	69
1	-	2	2	1-18028-4	WASHER, FLAT, REG M3	68
	-	1	1	2119740-1	TAG, IDENTIFICATION	67
1	-	2	2	2168078-1	SCREW, DRIVE, RH, RoHS, 2 x .188	66
	-	2	2	2-18032-5	SCR, SET, FLT PNT, M5 X 20.0	61
1	-	1	1	2079383-4	SCR, BHSC, RoHS (M4 X 8)	60
	-	1	1	5-18022-5	SCR, HEX HD CAP, M4 X 6.0	59
1	-	1	1	462427-2	FINGER, FEED	56
	-	4	4	2168400-1	SHCS, LOW HEAD, RoHS, M4 X 12	54
1	-	2	2	2-2168083-5	SCR, SKT HD CAP, RoHS, M4 X 14	53
	-	1	1	18023-9	SCR, SKT HD CAP M4 X 6.0	49
1	-	1	1	1-1803583-9	APPLICATOR BASIC ASSEMBLY, SF	46
	-	1	1	1803515-1	RAM ASSEMBLY, SF ATLANTIC	44
5	-	1	1	462433-7	SUPPORT, INSULATION	43
	-	1	1	1-462433-0	SUPPORT, INSULATION	42
5	-	1	1	1803602-1	SCR, BHSC, RoHS (M8 X 25)	41
	-	2	2	5-22278-1	SPRING, COMPRESSION	33
1	-	2	2	1-2168083-4	SCR, SKT HD CAP, RoHS, M4 X 5	30
	-	1	1	2161336-2	PLATE, REAR STRIP GUIDE	29
1	-	2	2	22281-9	SPRING, COMPRESSION	27
	-	1	1	356835-1	LEVER, DRAG RELEASE	26
1	-	1	1	240792-1	DRAG, TERMINAL	25
	-	1	1	684042-4	GUIDE, STRIP, FRONT	24
5	-	1	1	980371-4	SCR, SKT HD SHLDR 5.0 DIA X 6.0	23
	-	1	1	462431-6	WIRE FUNNEL	22
1	-	1	1	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	21
	-	1	1	1-18028-2	WASHER, FLAT, REG M4	20
1	-	1	1	2119533-1	STRIPPER, SIDE FEED	19
	-	1	1	463460-2	HOLD DOWN, TERMINAL	18
1	-	1	1	469542-3	REAR FLOATING SHEAR	17
	-	2	2	1-2168083-1	SCR, SKT HD CAP, RoHS, M3 X 6	16
1	-	1	1	2161335-2	SHEAR PLATE, REAR	15
	-	1	1	2119862-2	SHEAR HOLDER, REAR	14
1	-	1	1	2280441-1	INSERT, SHEAR	13
	-	1	1	3-22280-3	SPRING, COMPRESSION	12
5	-	1	1	1-356885-4	STOP, SHEAR	11
	-	1	1	462843-6	TERMINAL SUPPORT	10
5	-	1	1	462843-8	TERMINAL SUPPORT	9
	1	2	1	464291-4	ANVIL, SAND-BLASTED 22-18	8
4	-	1	1	803925-2	GUIDE, CARRIER SCRAP	7
	-	1	1	2-690468-5	DEPRESSOR SHEAR, REAR	6
5	-	1	1	462431-3	WIRE FUNNEL	5
	-	1	1	238011-1	BLOCK, CRIMPER SPACER	4
1	1	2	1	464290-1	CRIMPER, SEMI-FLAT 22-18	1

-77-72 -2		PART NO		DESCRIPTION		ITEM NO
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE TO BE HOLE LOCATIONS UNLESS OTHERWISE SPECIFIED. FOR THE LATEST REVISION.						
DWG		15JUN2012		 TE Connectivity Harrisburg, PA 17105-3608		
B. WEAVER		15JUN2012				
C. HOFFNER		15JUN2012				
T. FLINN		15JUN2012				
APVD				NAME		
TOLERANCES, UNLESS OTHERWISE SPECIFIED:				Ocean Side Feed Applicator		
0 PLC ±		PRODUCT SPEC		-		
1 PLC ±		-		-		
2 PLC ±		APPLICATION SPEC		-		
3 PLC ±		-		-		
4 PLC ±		-		-		
ANGLES ±		-		-		
FINISH		WEIGHT		SIZE		RESTRICTED TO
-		-		A 1 00779 ©=2151698		-
Customer Accessible Production Drawing				SCALE 1:1		SHEET 1 OF 4 REV F


THIS DOCUMENT IS UNPUBLISHED. IT IS SUBJECT TO CHANGE AND SHOULD BE CONTACTED FOR THE LATEST EDITION.		DWN B. WEAVER CHK G. HOFENER APVD T. ELBIN	15JUN2012 15JUN2012 15JUN2012	TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Ocean Side Feed Applicator	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES		± ± ± ± ± ±		PRODUCT SPEC	
MATERIAL		FINISH		APPLICATION SPEC	
-		-		WEIGHT	
-		-		A1 00779 ©=2151698	
-		-		Customer Accessible Production Drawing	
-		-		SCALE 1:1	
-		-		SHEET 1 OF 4	
-		-		REV F	

SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A	66	-	-	SEE SHEET 1	-	-	-

FEED TYPE

PNEUMATIC




FEED SPRING SETTING POSITION
(SHOWN FROM REAR SIDE)





DETAIL A


CAM POSITIONS



AIR FEED



RAM SET-UP



LOWER TOOLING SET-UP

ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE AND SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN B. WEAVER 15JUN2012	TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK G. HOFFNER 15JUN2012	NAME Ocean Side Feed Applicator	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD T. ELBIN 15JUN2012	SIZE A1	
MATERIAL -		PRODUCT SPEC APPLICATION SPEC WEIGHT -	CAGE CODE 00779	
		Customer Accessible Production Drawing	SCALE 1:1	
			SHEET 2 of 4	
			REV F	

8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
2012		2012	
(C) COPYRIGHT 2012 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.			
PART NUMBER	REVISION	DESCRIPTION	FEED TYPE
2-2151698-2	F	FINE CRIMP HEIGHT ADJUST	PNEUMATIC
7-2151698-7	A	CRIMP TOOLING KIT	-


APPLICATOR DATA		
CRIMP	SIZE	TYPE
WIRE	.176 [4.47 mm]	Ø
INSUL	-	-
APPLICATOR INSTRUCTIONS 408-35042		

TERMINAL DATA: TE TERMINAL TE CRIMP SPECIFICATION			
TERMINAL NAME: FULLY INSULATED FASTON			
WIRE STRIP LENGTH .265-.297 IN [6.73-7.54 mm]		INSULATION DIAMETER RANGE Ø 9	
TERMINAL APPLICATION SPECIFICATION 114-2123		-	-
TERMINALS APPLIED 3		-	-
TE TERMINAL	TE TERMINAL	TE TERMINAL	TE TERMINAL
2-520080-2	9-520272-2	2-520306-2	
2-520083-2	2-521010-2	2-520310-2	
2-520272-2			


GROUP 1 7 8		GROUP 2 7 8	
WIRE SIZE	CRIMP HEIGHT INCH [mm]	CRIMP HEIGHT REFERENCE SETTING	Ø SOLDER 9
18	0.070+/-0.002 [1.78+/-0.05]	6.3	.12 IN [3.05mm]
20 or 22	0.065+/-0.002 [1.65+/-0.05]	7.7	.12 IN [3.05mm]



- 1 RECOMMENDED SPARE PARTS
- 2 REFER TO SUPPLIED INSTRUCTION SHEET FOR CLEANING, LUBRICATION AND STORAGE OF APPLICATOR.
- 3 CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.
- 4 ITEM 7 MUST BE REMOVED IF APPLICATOR IS USED ON BENCH MACHINE.
- 5 ITEMS 5 AND 9 OR ITEMS 10 AND 22 ARE REQUIRED WHEN RUNNING ON A LEADMAKER.
ITEM 42 OR 43 REQUIRED WHEN RUNNING ON A BENCH MACHINE.
- 6 FEED ADJUSTMENT MAY BE REQUIRED WHEN SWITCHING TERMINALS.
- 7 GROUP 1 TERMINALS: Ø.120 IN [3.05mm] MAX INSULATION
GROUP 2 TERMINALS: Ø.200 IN [5.08mm] MAX INSULATION
- 8 USE ITEMS 5, 9, OR 42 WITH GROUP 1 TERMINALS
USE ITEMS 10, 22, OR 43 WITH GROUP 2 TERMINALS
- 9 TO CHECK CRIMP HEIGHT, CRIMP SOLDER (Ø.12 IN [3.05mm] 60/40 SOLID CORE) AND MEASURE AT CENTER OF SLUG.




- 10 IT MAY BE NECESSARY TO MODIFY THE T-TERMINATING/K-PRESS BASE PLATE BEFORE USE BY ADDING A 10-32 HOLE TO RELOCATE THE FORWARD STOP AS SHOWN.



- 1 ITEMS 253 AND 255 MUST BE INSTALLED IN THE G-TERMINATING UNIT CHIP RELIEF HOLE BEFORE INSTALLING THE APPLICATOR.
- 2 ITEM 257, REQUIRED IF APPLICATOR IS RUN ON T-TERMINATING UNIT/K-PRESS. GUARD, ITEM 256, REQUIRED IF APPLICATOR IS BEING USED ON G-TERMINATOR.
- 3 TERMINAL PITCH NOT COMPATIBLE WITH MECHANICAL FEED.

14. UNLESS SPECIFIED OTHERWISE TORQUE VALUES SHALL BE USED PER DOCUMENT, 101-35000.

PACIFIC VERSION TERMINATOR
INTERFACE ADAPTER



*WARNING
ON INSTALLATION, SET WIRE DISC TO CRIMP HEIGHT REFERENCE SETTING FOR LARGEST WIRE SIZE. CRIMP HEIGHT REFERENCE SETTINGS GREATER THAN THE VALUE SHOWN MAY CAUSE DAMAGE TO THE CRIMP TOOLING, REFER TO THE INSTRUCTION SHEET FOR PROPER SETUP AND ADJUSTMENTS.

PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)







LOC		DIST		REVISONS			
A	66	P	LTR	DESCRIPTION		DATE	OWN
		-		SEE SHEET 1		-	-

2	-	REF	462992-7	GUARD ASSEMBLY	257
	-	REF	679532-1	INSERT, GUARD	256
1	-	1	189728-1	BRACKET, SPACER	255
	-	1	568681-1	SPACER, BASE PLATE	253
1	-	1	7-18023-7	SCR, SKT HD CAP M3 X 4.0	241
	-	1	2844940-2	AIR FEED MODULE	238
1	-	1	1-18028-0	WASHER, FLAT, REG M8	192
	-	REF	994970-2	COUNTER, MAGNETIC	164
1	-	1	2119641-2	FEED CAM, AIR FEED	151
	-	1	2079383-8	SCR, BHSC, RoHS (M4 X 16)	144
1	-	4	2168400-5	SHCS, LOW HEAD, RoHS, M4 X 20	143
	-	1	2-1803583-0	APPLICATOR BASIC ASSEMBLY, SF	141
1	-	1	1803516-1	RAM ASSEMBLY, SF PACIFIC	140
	-	1	1-22281-8	SPRING, COMPRESSION	121
1	-	1	1-18028-2	WASHER, FLAT, REG M4	119
	-	1	2844908-1	SCREW, LOCKING	99
1	-	1	2844907-1	POST, LOCKING	98
	-	1	1-690438-0	FRONT STRIP GUIDE	96
1	-	2	2168083-1	SCR, SKT HD CAP, RoHS, M3 X 8.0	95
	-	4	18023-4	SCR, SKT HD CAP M3 X 10.0	94
1	-	1	2168083-6	SCR, SKT HD CAP, RoHS, M5 X 65	93
	-	1	455888-4	SPACER, CRIMPER	82
1	-	1	240641-9	SPACER	81
	-	1	1803607-3	DOCUMENTATION PACKAGE	71
1	-	1	2161332-2	DEPRESSOR, WIRE FUNNEL	70
	-	1	2161331-1	SPACER, WIRE FUNNEL DEPRESSOR	69
1	-	2	1-18028-4	WASHER, FLAT, REG M3	68
	-	1	2119740-1	TAG, IDENTIFICATION	67
1	-	2	2168078-1	SCREW, DRIVE, RH, RoHS, 2 x .188	66
	-	2	2-18032-5	SCR, SET, FLT PNT, M5 X 20.0	61
1	-	1	5-18022-5	SCR, HEX HD CAP, M4 X 6.0	59
	-	1	462427-2	FINGER, FEED	56
1	-	2	2-2168083-5	SCR, SKT HD CAP, RoHS, M4 X 14	53
	-	1	18023-9	SCR, SKT HD CAP M4 X 6.0	49
5	-	1	462433-7	SUPPORT, INSULATION	43
	-	1	1-462433-0	SUPPORT, INSULATION	42
5	-	1	1803602-1	SCR, BHSC, RoHS (M8 X 25)	41
	-	2	5-22278-1	SPRING, COMPRESSION	33
1	-	2	1-2168083-4	SCR, SKT HD CAP, RoHS, M4 X 5	30
	-	1	2161336-2	PLATE, REAR STRIP GUIDE	29
1	-	2	22281-9	SPRING, COMPRESSION	27
	-	1	356835-1	LEVER, DRAG RELEASE	26
1	-	1	240792-1	DRAG, TERMINAL	25
	-	1	684042-4	GUIDE, STRIP, FRONT	24
5	-	1	980371-4	SCR, SKT HD SHLDR 5.0 DIA X 6.0	23
	-	1	462431-6	WIRE FUNNEL	22
1	-	1	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	21
	-	1	1-18028-2	WASHER, FLAT, REG M4	20
1	-	1	2119533-1	STRIPPER, SIDE FEED	19
	-	1	463460-2	HOLD DOWN, TERMINAL	18
1	-	1	469542-3	REAR FLOATING SHEAR	17
	-	2	1-2168083-1	SCR, SKT HD CAP, RoHS, M3 X 6	16
1	-	1	2161335-2	SHEAR PLATE, REAR	15
	-	1	2119862-2	SHEAR HOLDER, REAR	14
1	-	1	2280441-1	INSERT, SHEAR	13
	-	1	3-22280-3	SPRING, COMPRESSION	12
1	-	1	1-356885-4	STOP, SHEAR	11
	-	1	462843-6	TERMINAL SUPPORT	10
5	-	1	462843-8	TERMINAL SUPPORT	9
	1	1	464291-4	ANVIL, SAND-BLASTED 22-18	8
4	-	1	803925-2	GUIDE, CARRIER SCRAP	7
	-	1	2-690468-5	DEPRESSOR SHEAR, REAR	6
5	-	1	462431-3	WIRE FUNNEL	5
	-	1	238011-1	BLOCK, CRIMPER SPACER	4
1	1	1	464290-1	CRIMPER, SEMI-FLAT 22-18	1

-77 -22		PART NO	DESCRIPTION		ITEM NO
OWN B. WEAVER		15JUN2012	 TE Connectivity Harrisburg, PA 17105-3608		NAME Ocean Side Feed Applicator
CHK G. HOFENER		15JUN2012			
APVD T. ELBIN		15JUN2012			
PRODUCT SPEC					
APPLICATION SPEC			SIZE		CAGE CODE
MATERIAL			DRAWING NO		RESTRICTED TO
FINISH			00779		REV
Customer Accessible Production Drawing		SCALE	1:1	SHEET	3 OF 4

SHEETS 1 & 2 ARE NOT REQUIRED FOR PACIFIC VERSION

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
A	66	-	-	SEE SHEET 1	-	-



PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

1. THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING MUST BE APPROVED BY THE DESIGNING ORGANIZATION. 2. THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING MUST BE APPROVED BY THE DESIGNING ORGANIZATION.		DWN B. WEAVER 15JUN2012	TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK G. HOFFNER 15JUN2012	NAME Ocean Side Feed Applicator	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		APVD T. ELBIN 15JUN2012	PRODUCT SPEC APPLICATION SPEC	
MATERIAL		SIZE A1	CAGE CODE 00779	DRAWING NO. C=2151698
Customer Accessible Production Drawing		SCALE 1:1	SHEET 4	OF 4
		REV F		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2151698-2](#)