



2378366-1
AS SHOWN




NOTES;


- 1 TE ORDER-NUMBER
- 2 TE LOGO
- 3 SECONDARY LOCK IN PRE-LOCK POSITION
- 4 CONTACT CAVITY MARKING
- 5 SLIDING DISTANCE OF SECONDARY LOCKING
6. SUITABLE COVER SEE DRAWING - 2378357-1
- 7 TRAY PACKAGING IN CORRUGATED BOX.
- 8 LEVER DELIVERY CONDITION.
9. MATING ASSEMBLY PN - 2378367-1/-2
10. CONTACT AND APPLICABLE WIRE DETAILS REFFER TABLE

TERMINAL TYPE	TERMINAL GROUP DRAWING	TERMINAL PART NUMBER	WIRE SIZE(mm ²)
1.2 MCON	1534326	1534594-X	0.35
		1670144-X	0.5-0.75
2.8 AMP MCP	1355036	X-968855-X	0.5-1.0
		X-968857-X	1.0-2.5
6.3 AMP MCP	1241438	1241416-X	2.5-4.0
		X-1241418-X	4.0-6.0


11. MALFUNCTION CAUSED BY LACQUER IS NOT COVERED BY TE CONNECTIVITY WARRANTY.
12. SUITABLE CAVITY PLUG / SEALING PLUG FOR MCON 1.2 PN# 1-2109258-8, 1-1452424-2. FOR AMP MCP 2.8K PN# 0-828922-1 FOR AMP MCP 6.3K PN# 0-100132-1



8 LEVER PRE-LOCK CONDITION





DELIVERY CONDITION OF SEC LOCK IN PRE LOCKED CONDITION




DELIVERY CONDITION OF SEC LOCK IN PRE LOCKED CONDITION

DELIVERY CONDITION OF SEC LOCK IN PRE LOCKED CONDITION

2378366-2
AS SHOWN



PANEL THICKNESS=2.0±0/-0.1



						
1	1	A	58POS. MCON SEC LOCK	PBT-GF20	YELLOW	8
1	1	A	58POS. LEVER	PBT-GF20	RED	7
1	1	A	58POS. HYBRID RECP INNER HSG. W-W	PBT-GF15	BLACK	6
2	2	A	58POS. RECEP SEC LOCK	PBT-GF20	YELLOW	5
1	1	A	58POS. PERIPHERAL SEAL	LIQUID SILICON	GREEN	4
1	1	A	58POS. FAMILY SEAL FOR RECEPTACLE AND TAB SIDE	SOLID SILICON	LIGHT BLUE	3
1	-	A	58POS.HYBRID RECP OUTER HSG. W-W, CODE B	PBT-GF15	SIGNAL BLUE	2
-	1	A	58POS.HYBRID RECP OUTER HSG. W-W, CODE A	PBT-GF15	BLACK	1
0-2	0-1	REV	DESCRIPTION	MATERIAL	COLOUR	ITEM NO
A	A	REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)				
80	80	WEIGHT OF EACH ASSY NO [g]				
QTY REQD PER ASSY						

TOLERANCING EN ISO 8015		DWN PAVAN G 12NOV2021
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		CHK SHIVAKUMAR H 12NOV2021
DIMENSIONS: mm		APVD GURUMURTHY CR 13NOV2021
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC
0-PLC ±		108-94852
1-PLC ±0.1		APPLICATION SPEC
2-PLC ±0.01		114-94739
3-PLC ±0.001		WEIGHT
4-PLC ±0.0001		SEE TABLE
ANGLES ±		CUSTOMER DRAWING
MATERIAL SEE TABLE		FINISH -

TE Connectivity		NAME 58POS.HYBRID.RECEP HSG ASSY.SLD	
SIZE A2		CAGE CODE 00779	DRAWING NO C-2378366
RESTRICTED TO -		SCALE 1:1	SHEET 1 OF 1
REV A5			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2378366-2](#)