





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-24-198159	23JAN2024	ED	WH



- NOTES:
- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
  - 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
  - 3 ELECTRICAL CHARACTERISTICS :  
FREQUENCY RANGE : DC-2GHz  
NOMINAL IMPEDANCE : 50 OHMS  
INSULATION RESISTANCE : 5000 MOHMS  
WORKING VOLTAGE : 335 VRMS MAX  
DIELECTRIC WITHSTANDING VOLTAGE : 750 VOLTS MAX  
VSWR : 1.5 MAX(DC-2GHz)  
CONTACT RESISTANCE :  
CENTER CONTACT : 3 mOHMS MAX  
OUTER CONTACT : 2 mOHMS MAX;
  - 4 MECHANICAL CHARACTERISTICS :  
DURABILITY : 500 CYCLES
  - 5 TEMPERATURE RANGE: -65°-+165°;
  - 6 RoHS: COMPLIANT.

	1	NATURAL	PTFE	INSULATOR	5
	1	GOLD 50u"/NICKEL/COPPER	BRASS	CONTACT PIN	4
	1	GOLD 50u"/NICKEL/COPPER	BERYLLIUM COPPER	CONTACT PIN	3
	1	NATURAL	PTFE	INSULATOR	2
	1	BRIGHT TIN 200u"/ NICKEL/COPPER	ZINC DIECAST	BODY	1
	2466267-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 11SEP2023	TE Connectivity		
		CHK ED 11SEP2023			
DIMENSIONS: mm		APVD WH 11SEP2023	NAME BNC JACK,PCB MOUNTING HOLE, RIGHT ANGLE,2GHZ		
		PRODUCT SPEC	-		
		APPLICATION SPEC	-		
MATERIAL SEE TABLE		WEIGHT 0	SIZE A2	CAGE CODE 00779	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 8:1	SHEET 1 OF 1
				REV A1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2466267-1](#)