





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-24-198159	23JAN2024	ED	WH



PCB MOUNTING HOLE



NOTES:

- PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- ELECTRICAL CHARACTERISTICS :  
FREQUENCY RANGE : DC-3GHz  
NOMINAL IMPEDANCE : 75 OHMS  
INSULATION RESISTANCE : 5000 MOHMS  
WORKING VOLTAGE : 335 VRMS MAX  
DIELECTRIC WITHSTANDING VOLTAGE : 750 VOLTS MAX  
VSWR : 1.2 MAX (DC-3GHz)  
CONTACT RESISTANCE :  
    CENTER CONTACT : 3 mOHMS MAX  
    OUTER CONTACT : 2 mOHMS MAX;
- MECHANICAL CHARACTERISTICS :  
DURABILITY : 500 CYCLES
- TEMPERATURE RANGE: -65°-+165°;
- RoHS: COMPLIANT.

	1	NATURAL	PTFE	INSULATOR	5
	1	GOLD 50u"/NICKEL/COPPER	BRASS	CONTACT PIN	4
	1	GOLD 50u"/NICKEL/COPPER	BERYLLIUM COPPER	CONTACT PIN	3
	1	NATURAL	PTFE	INSULATOR	2
	1	NICKEL 100u"/COPPER	ZINC DIECAST	BODY	1
	2466268-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 03JUL2023	TE Connectivity		
		CHK ED 03JUL2023			
DIMENSIONS: mm		APVD WH 03JUL2023	NAME BNC JACK,PCB MOUNTING HOLE, RIGHT ANGLE,75OHM,3GHZ		
		PRODUCT SPEC	-		
		APPLICATION SPEC	-		
		WEIGHT	-		
MATERIAL SEE TABLE		CUSTOMER DRAWING		SIZE A2	RESTRICTED TO -
				CAGE CODE 00779	
				DRAWING NO C-2466268	
				SHEET 1 OF 1	REV A1
				SCALE 8:1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2466268-1](#)