





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-231221)	15SEP2023	ED	WH



RECOMMENDED  
MOUNTING HOLE

- NOTES:
- PACK IN ACCORDANCE WITH TE SPEC 107-3275;
  - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
  - ELECTRICAL CHARACTERISTICS :  
FREQUENCY RANGE : DC-18GHz  
NOMINAL IMPEDANCE : 50 OHMS  
INSULATION RESISTANCE : 5000 MOHMS  
WORKING VOLTAGE : 335 VRMS MAX  
DIELECTRIC WITHSTANDING VOLTAGE : 750 VOLTS MAX  
VSWR : 1.2(DC-18GHz)  
CONTACT RESISTANCE :  
CENTER CONTACT : 3 mOHMS MAX  
OUTER CONTACT : 2 mOHMS MAX;
  - MECHANICAL CHARACTERISTICS :  
DURABILITY : 500 CYCLES  
TORQUE SETTING(SMA) : 7-10 IN-LBS;
  - TEMPERATURE RANGE: -65°-+165°;
  - RoHS: COMPLIANT.

	1	-	FLUOROSILICONE	GASKET	6
	1	PASSIVATED	STAINLESS STEEL	HEX NUT	5
	1	PASSIVATED	STAINLESS STEEL	LOCK RING	4
	1	GOLD 50u"/ NICKEL/COPPER	BERYLLIUM COPPER	CENTER CONTACT	3
	1	NATURAL	PTFE	INSULATOR	2
	1	PASSIVATED	STAINLESS STEEL	BODY	1
	2466280-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY			PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN ED 13SEP2023	TE Connectivity	
			CHK ED 13SEP2023		
DIMENSIONS: mm			APVD WH 13SEP2023	NAME ADAPTER,SMA JACK TO BMA PLUG, STRAIGHT,BULKHEAD,18GHZ	
			PRODUCT SPEC	SIZE A2	
			APPLICATION SPEC	CAGE CODE 00779	
MATERIAL SEE TABLE			WEIGHT 0	DRAWING NO C-2466280	
			CUSTOMER DRAWING		RESTRICTED TO -
			SCALE 8:1	SHEET 1 OF 1	REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2466280-1](#)