


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-233095)	28SEP2023	ED	WH



NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3 ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-18GHz
NOMINAL IMPEDANCE : 50 OHMS
POWER RATING: 1W
VSWR : 1.25(DC-18GHz)
- 4 MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES
- 5 TEMPERATURE RANGE: -40°-+125°;
- 6 RoHS: COMPLIANT.

	1	GOLD 30u"/ NICKEL/COPPER	BERYLLIUM COPPER	OUTER CONTACT	4
	1	GOLD 30u"/ NICKEL/COPPER	BERYLLIUM COPPER	CENTER CONTACT	3
	1	NATURAL	PTFE	INSULATOR	2
	1	GOLD 30u"/ NICKEL/COPPER	BRASS	BODY	1
	2467917-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 11JUL2023	TE Connectivity		
		CHK ED 11JUL2023			
		APVD WH 11JUL2023	NAME SMP FEMALE TERMINATION, STRAIGHT,18GHZ		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC		
		0 PLC ± 0.3	APPLICATION SPEC		
		1 PLC ± 0.2	WEIGHT		
		2 PLC ± 0.1	SIZE		
		3 PLC ± -	CAGE CODE		
		4 PLC ± -	DRAWING NO		
		ANGLES ± 5°	RESTRICTED TO		
MATERIAL		FINISH	SCALE		
SEE TABLE		-	SHEET		
			REV		
			A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2467917-1](#)