























LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN   APVD
CM	0	C		ECO-06-013157	17JUN06	BSV   DC



RECOMMENDED MOUNTING HOLE PATTERN  
FOR 1.78 MAX THICK P.C. BOARD  
COMPONENT SIDE SHOWN

- 1 MATERIAL:  
HOUSING: NYLON, UL94V-2 (COLOR - NATURAL, COLOR OF PARTS MAY VARY).  
CONTACTS: 0.25 THK COPPER ALLOY.
- 2 CONTACT FINISH: 0.003 MIN THK TIN-LEAD OVER 0.00127 MIN THK NICKEL OVER ENTIRE CONTACT.
- 3 CONTACT FINISH: 0.00076 MIN THK GOLD PLATE ON PIN MATING SURFACE, 0.003 MIN THK TIN-LEAD PLATE ON SOLDER TAIL, ALL OVER 0.00127 MIN THK NICKEL BASE PLATE.
4. SOLDER TAIL MEETS AMP SOLDERABILITY SPECIFICATION 109-11-2.
5. MATES WITH SIMILARLY PLATED AMP-DUAC™ POWER CONNECTOR RECEPTACLE HOUSINGS/SOCKET CONTACTS.
- 6 RIBS ON FOUR CORNERS OPTIONAL.
- 7 AMP LOGO AND MATERIAL ID MAY BE LOCATED ON EITHER LONG SIDE OF PART.
- 8 SIZE, SHAPE OR STYLE OF THIS FEATURE MAY VARY.
- 9 CONTACT FINISH: 0.003 MIN THK TIN OVER 0.00127 MIN THK NICKEL OVER ENTIRE CONTACT.
- 10 CONTACT FINISH: 0.00076 MIN THK GOLD PLATE ON PIN MATING SURFACE, 0.003 MIN THK TIN PLATE ON SOLDER TAIL, ALL OVER 0.00127 MIN THK NICKEL BASE PLATE.



					1-794350-2				
					1-794350-1				
SUPERCEDED BY 1-794350-2					794350-2				
SUPERCEDED BY 1-794350-1					794350-1				
MATERIAL		FINISH		MATERIAL	COLOR	PART NO.			
CONTACT		HOUSING							
THIS DRAWING IS A CONTROLLED DOCUMENT.									
<div>DIMENSIONS:</div> <div>mm</div> <div></div>		<div>TOLERANCES UNLESS OTHERWISE SPECIFIED:</div> <div>0 PLC ± -</div> <div>1 PLC ± 0.2</div> <div>2 PLC ± 0.13</div> <div>3 PLC ± -</div> <div>4 PLC ± -</div> <div>ANGLES ± 0°30'</div>		DWN R VESTAL 03/JUN/98			Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
				CHK R SWING 03/JUN/98					
		PART C CASH 03/JUN/98		NAME		ASSEMBLY, HEADER, VERTICAL, 4 POSITION, W/DRAIN HOLES, 94V-2,AMP-DUAC			
		PRODUCT SPEC							
		108-1699							
		APPLICATION SPEC							
		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		FINISH		A1		00779	C-794350	-	
SEE TABLE		SEE TABLE		CUSTOMER DRAWING		SCALE	5:1	SHEET 1 OF 1	REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-794350-1](#)