

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 19

RELEASED FOR PUBLICATION  
BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

19

LOC DIST

G 14

P

F

ZONE

LTR

D

EC 0720-0279-93

REVISIONS

DESCRIPTION

DATE

APPD



6-18-93

556 BB


D

2

D



1. TONGUE MATERIAL THK 1.02±0.08[.040±.003]  
FOR 6.50[.256] MAX WIRE INS DIA



AMP INCORPORATED  
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTS  
1-800-522-6752

FOR APPLICATION  
TOOLING ASSISTANCE CENTER  
1-800-722-1111

FOR ORDER ENTRY  
1-800-526-5142

MAX RECOMMENDED OPERATING  
TEMPERATURE:  
105°C

VOLTAGE RATING:  
-

CIRCULAR MIL AREA:  
6.64-10.5mm² [13,100-20,800]  
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MS25036-117  
CLASS 2

MILITARY P/N AND CLASS

QTY

LOOSE PC

324044

PACKAGE TYPE

PART NO

AMP

AMP Incorporated  
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, TERMINYL  
WIRE SIZE: 8 AWG

SIZE CASE CODE DRAWING NO

B 00779 C-324044

SCALE

NTS

SHEET

1 OF 1

AMP 1470-15 REV 3-92

21 JUN 1993

10:12:51

AMPT1122

<U0128A>DEPT1132>AMPT1122>U.CUSTOMINYL

CUSTOMER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MS25036-117](#)