





LOC		DIST	P		F	ZONE	LTR	REVISIONS		DATE	APPD
GP	00							AF	REVISED PER 0651-0122-98	8/14/98	RB
								AG	REACTIVATE PART 24 PER 051B-0011-00	01/25/00	MM
								AG	ADD PART -82 PER 051B-0219-00	10/18/00	JB
								AJ	REV PER EC 051B-0239-00	10/08/00	NF
								AK	ADDED -83 PER EC 0512-0061-01	04 DEC 01	AF
								AL	REV PER EC 0512-0112-01	17 JUN 02	AF



- 1 HOUSING: GLASS FILLED POLYESTER; COLOR: BLACK.
- 2 CONTACT: PHOSPHOR BRONZE.
- 3 NICKEL PLATE: 0.00127 [.000050] MIN - ALL OVER.
- 4 TIN-LEAD PLATE: 0.00254 [.000100] MIN - SOLDER POSTS.
- 5 GOLD PLATE: 0.00038 [.000015] MIN - CONTACT AREA.
- 6 GOLD PLATE: 0.00076 [.000030] MIN - CONTACT AREA.
- 7 NICKEL PLATE PER MIL-G-45204.
GOLD PLATE PER QQ-N-290.
- 8 AMP PART NUMBER, DATE CODE AND CSA LOGO MAY BE MARKED
IN APPROXIMATE AREA SHOWN, EITHER SIDE.
9. RECOMMENDED PCB FINISHED HOLE DIA: 1.02±0.08 [.040±.003].



DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± -		DR 10/2/91 K.L.CLOUSER/UTA		AMP AMP Incorporated Harrisburg, PA 17105-3608			
MATERIAL HOUSING:  CONTACT: 		CHK 3-6-92 J DIORAZIO	APPD 3-6-92 J DIORAZIO				NAME CONNECTOR ASSEMBLY, STANDARD EDGE II, 2.54 [.100] CL
		APPD 3-6-92 M THUMMA	PRODUCT SPEC 108-9039				
FINISH CONTACT:     		APPLICATION SPEC -	SIZE 	CAGE CODE 00779	DRAWING NO 530843		
		WEIGHT -	SCALE 5:1	SHEET 1 OF 2			

DRAWING MADE IN THIRD ANGLE PROJECTION		THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		,19			
© COPYRIGHT 19		BY AMP INCORPORATED.		ALL INTERNATIONAL RIGHTS RESERVED.					

LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
GP		00						AL		SEE SHEET 1				-		-	

--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

-
- Home

Part Number Search

Document Search

Text Search

Alternate Part Search

Multiple Part Comparison

Alphabetical Search

Brand Search

Industry Product Search

Product Type Search

Product Family Search

Competitor Cross Reference

Lead Free Solutions

Help/Glossary

Current Brand View

AMP

[View All Tyco Electronics Brands](#)
Click to activate links to all other products

Card Edge Connectors

ISA Connectors (Standard Edge II & III+)

AMP

1-530843-3

Active

[Active](#)

(Tyco Electronics P/N: 1-530843-3)

[CAD Geometry](#) | [Search for Parts](#) |

P

[Previous](#) [1](#) [2](#) [3](#) **[4]** [5](#) [Next](#)

N

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info Sales Info Assembly Subcontractors	Pricing Product Availability	

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[PCB Layout](#)

[Recommended PC Board Edge Pattern](#)

Searchable Features:	
Brand:	AMP
Product Type:	Connector
Product Series:	Standard Edge II
Connector Type:	Standard
Centerline (mm [in]):	2.54 [0.100]
No. of Dual Positions:	15
Post Type:	Solder Post
Contact Mating Area Plating:	Gold (30)
Termination Post Length (mm [in]):	4.75 [0.187]
PCB Mount Angle:	Vertical

Other Properties:	
Contact Material:	Phosphor Bronze
Contact Termination Area Plating:	Tin
Contact Underplating:	Nickel
Housing Material:	Glass-Filled Polyester
Housing Color:	Black
Housing Flammability Rating:	UL 94V-0

Mounting Ears:	Without
PCB Retention Feature:	Without
Retention Latch:	Without

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Customer Service](#) | [About](#) | [Home](#)

-
- Home

Part Number Search

Document Search

Text Search

Alternate Part Search

Multiple Part Comparison

Alphabetical Search

Brand Search

Industry Product Search

Product Type Search

Product Family Search

Competitor Cross Reference

Lead Free Solutions

Help/Glossary

Current Brand View

AMP

View All Tyco Electronics Brands

Click to activate links to all other products

Card Edge Connectors

ISA Connectors (Standard Edge II & III+)

AMP530843-2ActiveActive

(Tyco Electronics P/N: 530843-2)

CAD Geometry | Search for Parts | Previous

12345Next

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info Sales Info Assembly Subcontractors	Pricing Product Availability	

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

PCB Layout

Recommended PC Board Edge Pattern

Searchable Features:	
Brand:	AMP
Product Type:	Connector
Product Series:	Standard Edge II
Connector Type:	Standard
Centerline (mm [in]):	2.54 [0.100]
No. of Dual Positions:	15
Post Type:	Solder Post
Contact Mating Area Plating:	Gold (30)
Termination Post Length (mm [in]):	3.18 [0.125]
PCB Mount Angle:	Vertical

Other Properties:	
Contact Material:	Phosphor Bronze
Contact Termination Area Plating:	Tin
Contact Underplating:	Nickel
Housing Material:	Glass-Filled Polyester
Housing Color:	Black
Housing Flammability Rating:	UL 94V-0

Mounting Ears:	Without
PCB Retention Feature:	Without
Retention Latch:	Without

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Customer Service](#) | [About](#) | [Home](#)

-
- Home

Part Number Search

Document Search

Text Search

Alternate Part Search

Multiple Part Comparison

Alphabetical Search

Brand Search

Industry Product Search

Product Type Search

Product Family Search

Competitor Cross Reference

Lead Free Solutions

Help/Glossary

Current Brand View

AMP

[View All Tyco Electronics Brands](#)
Click to activate links to all other products

Card Edge Connectors

ISA Connectors (Standard Edge II & III+)

AMP

530843-6

Active

Active

(Tyco Electronics P/N: 530843-6)

[CAD Geometry](#) | [Search for Parts](#) |

Previous

1

2

3

4

Next

N

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info Sales Info Assembly Subcontractors	Pricing Product Availability	

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[PCB Layout](#)

[Recommended PC Board Edge Pattern](#)

Searchable Features:	
Brand:	AMP
Product Type:	Connector
Product Series:	Standard Edge II
Connector Type:	Standard
Centerline (mm [in]):	2.54 [0.100]
No. of Dual Positions:	28
Post Type:	Solder Post
Contact Mating Area Plating:	Gold (30)
Termination Post Length (mm [in]):	3.18 [0.125]
PCB Mount Angle:	Vertical

Other Properties:	
Contact Material:	Phosphor Bronze
Contact Termination Area Plating:	Tin
Contact Underplating:	Nickel
Housing Material:	Glass-Filled Polyester
Housing Color:	Black
Housing Flammability Rating:	UL 94V-0

Mounting Ears:	Without
PCB Retention Feature:	Without
Retention Latch:	Without

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Customer Service](#) | [About](#) | [Home](#)

-
- Home

Part Number Search

Document Search

Text Search

Alternate Part Search

Multiple Part Comparison

Alphabetical Search

Brand Search

Industry Product Search

Product Type Search

Product Family Search

Competitor Cross Reference

Lead Free Solutions

Help/Glossary

Current Brand View

AMP

View All Tyco Electronics Brands

Click to activate links to all other products

Card Edge Connectors

ISA Connectors (Standard Edge II & III+)

AMP7-530843-7Active

[Active](#)

(Tyco Electronics P/N: 7-530843-7)

[CAD Geometry](#) | [Search for Parts](#) | [Previous](#) [1](#) [2](#) [3](#) [Next](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info Sales Info Assembly Subcontractors	Pricing Product Availability	

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[PCB Layout](#)

[Recommended PC Board Edge Pattern](#)

Searchable Features:	
Brand:	AMP
Product Type:	Connector
Product Series:	Standard Edge II
Connector Type:	Standard
Centerline (mm [in]):	2.54 [0.100]
No. of Dual Positions:	3
Post Type:	Solder Post
Contact Mating Area Plating:	Gold (30)
Termination Post Length (mm [in]):	3.18 [0.125]
PCB Mount Angle:	Vertical

Other Properties:	
Contact Material:	Phosphor Bronze
Contact Termination Area Plating:	Tin
Contact Underplating:	Nickel
Housing Material:	Glass-Filled Polyester
Housing Color:	Black
Housing Flammability Rating:	UL 94V-0

Mounting Ears:	Without
PCB Retention Feature:	Without
Retention Latch:	Without

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Customer Service](#) | [About](#) | [Home](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[530843-7](#) [7-530843-7](#)