


Technical drawing of a 12-pin connector. The drawing shows a top view of the connector with 12 pins arranged in a 3x4 grid. The pins are numbered 1 through 12. The dimensions are as follows:

- Overall width: $14,1 \pm 0,1$
- Pin pitch (center-to-center distance): $[0,31] = 7,78$
- Pin diameter: $[0,13]$
- Pin length: $[0,4]$
- Pin spacing (from center to edge): $[0,14] = 3,38$
- Overall height: $[0,59 \pm 0,002]$
- Pin spacing (from center to edge): $15 \pm 0,05$



-***
CD9 732-8260-20 X**

Annee/Year

Module suivant: EN4165

Température d'utilisation: -55°C à $+175^{\circ}\text{C}$

Matériaux: Thermoplastique et silicone

Tension de tenue: 1500 V eff; 50Hz

Contact à picot: Doré

Avant des contacts normalisés suivant: SAE/AS 39029/57-357

Masse: TBD

Dimensions: Millimètres [pouces]

Marquage sur la face opposée aux clés

Module according to: EN4165

Operating temperature range: -55°C à +175°C

Materials: Thermoplastique et silicone

Withstanding voltage: 1500 V ; 50Hz (RMS)



PCB pin contact: Gold plated

Front part contact as per: SAE/AS 39029/57-357

Weight: TBD

Dimension: Millimeters [inches]

1 Marking on the opposite keys side



O		02-12-2014	OE211114	SERIE	DMC-M Série II	DATE	09-12-2006	VISA Creation <i>Re</i>	VISA Approbation <i>D</i>
Revision	Date	Observations	DESIGNATION	Module S 12# 20 A PICOTS DROITS Socket Module 12# 20 with straight PCB contacts					
ORIGINE :				DE017706					
				REF : P/N: 732-8260-20 X					

DEUTSCH

Connecteurs Electriques Deutsch

17, rue LAVOISIER - BP 117 - 27091 EVREUX CEDEX 09 - FRANCE

204-119-A/101

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[732-8260-20](#)