


4

3

2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
A1	-					



Wire Range mm' AWG	Crimp Height mm	Insulation Range mm	Terminals
0,03-0,09 32-28	0,53 ^{+0,03}	1,4 max.	167023-2
0,20-0,56 24-20	0,77 ^{+0,03}	1,4 max.	141603-3
0,12-0,14 26	0,72 ^{+0,03}	0,5 - 1,0	141603-3

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±1°

FINISH -

DWN Ch.Witt 24OCT2005

CHK -

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT 330 g

CUSTOMER DRAWING

tyco Electronics

tyco Electronics AMP GmbH
D - 64625 Bensheim

NAME

HAND TOOL ASSEMBLY FOR MODU IV
Handzange für Modu IV

SIZE A3

CAGE CODE 00779

DRAWING NO © 169481-1

RESTRICTED TO -

SCALE -

SHEET 1 of 1

REV D

AMP 1470-19 REV 31MAR2000

Pro/ENGINEER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[169481-1](#)