

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		E1	ECR-21-100139	12 JAN 2021	KD	FL
			E2	ECR-21-100675	23 FEB 2021	KD	FL
			E3	ECR-21-102870	20 MAY 2021	SM	FL
			E4	ECR-21-103933	14 JUN 2021	PJ	FL

REMARKS/Bemerkungen

- 1

CAVITY SUITABLE FOR STANDARD TIMER CONTACTS LISTED IN PROD.SPEC. 108-18049. ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte gelistet in Prod. Spec. 108-18049. Punkt 3.3.2
- 2

CONTACT CAVITY NO.
Kontaktkammernummerierung
- 3

MATING STOP
Tiefenanschlag
- 4

AREA FOR TE LOGO ACC: TO SPEC 202-36
Bereich für TE Logo nach Spec. 202-36
- 5

POLARIZATION RIB POSITION "a" AND/OR "b"
Polarisierungsrippe Position "a" und/oder "b"
- 6

KEYING RIB POSITION "c" AND/OR "d"
Kodierrippe Position "c" und/oder "d"
- 6a

KEYING RIB POSITION "c" AND/OR "d" AT THE END WALLS OF THE HOUSING
Kodierrippe Position "c" und/oder "d" an den Gehäusestirnseiten
- 7

LOCKING LATCH
Rasthaken
- 8

TE PART NO (PN)
TE Bestell Nr. (PN)
- 9

DESIGN OF THE HOUSINGS ACC: TO RAST 5 STANDARD
Gehäuseausführung gemäß RAST 5 Vorgabe
- 10

GENERAL SUITABLE TAB HEADER SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwannen siehe RAST 5 Vorgabe
- 11

PACKAGING: BULK PACKAGING IN CORRUGATED BOX PN 740580-2
2 POS. 2500 PIECES PER BOX / 3 POS. 2000 PIECES PER BOX
Verpackung: Schüttgut in Versandkarton Pn 740580-2
2pol. 2500 Stück per Karton / 3pol. 2000 Stück per Karton
- 12

DIMENSION A, B C AND D SEE SHEET 2 OF 3
- 13

MATERIAL CORRESPONDS TO THE REQUIRMENT EN 60335
(INCL. GLOW WIRE TEST 750° WITHOUT FLAME)
Material entspricht den Anforderungen der EN 60335
(inkl. Glühdrahtfest 750° ohne Flamme)
- 14





RATIO NUMBER OF THE KEYING VERSION,INKJET PRINTED. SEE SHEET 2
Kodierungskennnummer, mit Tintenstrahlendrucker aufgebracht . siehe Blatt 2
- 15

PRELIMINARY- NOT RELEASED FOR PRODUCTION
- 16


ONLY FOR 9-1241961-7. DIMENSION 3.2 -0.2
- 17

DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL
- 18

ALLOWED 25±0.2 FOR P/Ns X-2364739-X.




SECTION A-A / Schnitt A-A



SECTION B-B / Schnitt B-B

5 POSITION
STD. TIMER MARK-II HOUSING



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Kishor M	18-10-07	 TE Connectivity			
DIMENSIONS: mm		CHK K.Muniz	18-10-07				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. Klender	18-10-07	NAME STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehaeuse RAST 5 Mark II			
		PRODUCT SPEC 108-18049-1		SIZE A1			
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 5 PLC ±0.2 6 PLC ±0.2 7 PLC ±0.2 8 PLC ±0.2 9 PLC ±0.2 10 PLC ±0.2 11 PLC ±0.2 12 PLC ±0.2 13 PLC ±0.2 14 PLC ±0.2 15 PLC ±0.2 16 PLC ±0.2 17 PLC ±0.2 18 PLC ±0.2	APPLICATION SPEC	WEIGHT -	CAGE CODE 00779			
				DRAWING NO 1241961			
MATERIAL SEE TABLES SHEETS PAGE 2 AND 3 OF 4		Customer Drawing		RESTRICTED TO -			
				SCALE 5:1			
				SHEET 1 of 4			
				REV E4			

A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

SPECIAL VERSION: UL94 V0 & GWEPT 750°C NF								
2364739-5	5	4	0.5	25	20	PA66 1317	BLUE	C
2364739-4	4			20	15		BLUE	C
1-2364739-3	3			15	10		BLUE	C
2364739-3				15	10		BLUE	C
1-2364739-2				10	5		BLUE	C
2364739-2	2			10	5		BLUE	C
3-2364739-2		2		10	5		BLUE	C
2-2364739-2				10	5		BLUE	C


SPECIAL VERSION: UL94 V0 & GWT 750 NF & CTI 350								
5-1241961-7	3	6	1	15	10	PA6613	NATURAL	A
1-1241961-9	3			15	10		NATURAL	A
7-1241961-7	3			15	10		NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
152322164-1	4	4	0.5	20	15	PA6613	NATURAL	1

SPECIAL VERSION: UL94 V2 & GWT 750 NF								
6-2178575-7	3	4	0.5	15	10	PA6 GF1513	NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
153-2178412-7	3	6	1	15	10	PA6613 UL94 V0 & GWT 750 NF	NATURAL	1
154-2178412-7	3			15	10		NATURAL	1
158-2178412-2	2			10	5		NATURAL	1

UL94 V0 & GWT 750 NF								
2322917-4	4	4	0.5	20	15	PA66 UL94 V0 & GWT 750 NF 13	NATURAL	C
2322917-2	2			10	5		NATURAL	C
2315717-1	2			10	5		NATURAL	C
2315717-2	2			10	5		NATURAL	C
2315717-3	2			10	5		NATURAL	C
1-2315717-2	2			10	5		NATURAL	1
152-2315717-2	2	4	0.5	10	5		NATURAL	1
2315717-4	4			20	15		NATURAL	C
2315717-5	4			20	15		NATURAL	C
2315717-6	3			15	10		NATURAL	C
2315717-7	3			15	10		NATURAL	C
1-2315717-3	3			15	10		NATURAL	E
PART NO.	POS	DIM C 12	DIM D 12	DIMA 12	DIM B 12	MATERIAL	COLOUR	REV.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN Kishor M	18-10-07	 TE Connectivity		
DIMENSIONS: mm				CHK K.Munz	18-10-07			
				TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T.Klanner	18-10-07	NAME
				0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±- 4 PLC ±- ANGLES ±° FINISH		PRODUCT SPEC 108-18049		STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II
MATERIAL SEE TABLES. SHEETS PAGE 2 AND 3 OF 4				WEIGHT -		SIZE A 1		00779
				Customer Drawing		CAGE CODE -		1241961
						RESTRICTED TO -		
						SCALE 5:1		SHEET 3
						OF 4		REV E 4

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

2 POSITION VARIANTS

2.00

0-969484-1

2.14

1-969484-1
2315717-2

2.13

2-969484-1

2.12

3-969484-1 OBSOLETE

2.11

4-969484-1

2.10

5-969484-1 OBSOLETE

2.09

6-969484-1

2.07

7-969484-1 OBSOLETE
3-2364739-2

2.06

8-969484-1

2.04

9-969484-1 OBSOLETE

2.03

0-969484-2

2.02

1-969484-2 OBSOLETE

2.08

2-969484-2

2.21

3-969484-2

2.99

4-969484-2
2315717-1

2.20

5-969484-2
2-2364739-2
PA6

2.19

6-969484-2
PA6

2.18

7-969484-2
PA6

2.17

8-969484-2
2315717-3
PA6

2.16

9-969484-2
PA6

2.31

0-969484-3

2.15

1-969484-3 OBSOLETE

2.05

2-969484-3 OBSOLETE

2.30

3-969484-3 OBSOLETE

Ohne/NONE

4-969484-3

Ohne/NONE

5-969484-3

Ohne/NONE

6-969484-3

Ohne/NONE

7-969484-3 OBSOLETE

5-1241961-2

0-1241961-1

2-1241961-2

3-1241961-2
PA6

6-1241961-2
2364739-2

7-1241961-2
2315717-2
PA6

8-1241961-2
2178412-2

9-1241961-2
PA6

0-1241961-3
1-2315717-2

3-1241961-3
PA6

4-1241961-3

5-1241961-3
PA6

6-1241961-3

7-1241961-3
1-2364739-2
2178571-2

6-1241983-2

8-1241983-2
PA6

5-1241983-3

PA6

0-1241983-2

1-1241983-2

2-1241983-2

3-1241961-1

8-1241961-3
2322917-2

4-1955422-3

9-1955506-2

0-1955422-1

PRELIMINARY

3 POSITION VARIANTS

3.00

0-969484-6 OBSOLETE

3.38

1-969484-6 OBSOLETE

3.18

2-969484-6

3.37

3-969484-6

3.35

4-969484-6 OBSOLETE

3.33

5-969484-6 OBSOLETE

3.32

6-969484-6 OBSOLETE

3.20

7-969484-6

3.10

8-969484-6

3.09

9-969484-6

3.08

0-969484-7 OBSOLETE

3.39

1-969484-7
1-1955422-7 PRELIMINARY

3.31

2-969484-7 OBSOLETE

3.40

3-969484-7

3.99

4-969484-7 OBSOLETE

Ohne/NONE

5-969484-7

3.45

6-969484-7 OBSOLETE

3.47

7-969484-7 OBSOLETE

3.65

8-969484-7

3.48

9-969484-7 OBSOLETE

3.66

0-969484-8

Ohne/NONE

1-969484-8 OBSOLETE

Ohne/NONE

2-969484-8

9-1241961-9

3-1241961-8

9-969484-9

4-1241961-8

5-1241961-8

0-1241961-6

2-1241961-7
5-1241961-7
2364739-3
2178571-1

1-1241961-8
PA6

6-1241961-8
7-1241961-7

2-1241961-8
PA6

7-1241961-8

1-1241961-7
PA6

8-1241961-8
1-2315717-3

03-K
2-1241817-3

0-1241961-8

PA6

3-1241961-7
4-1241961-7
5-1955422-7
6-2178575-7
2345753-1

03-F
3-1241961-7
4-1241961-7
5-1955422-7
6-2178575-7
2345753-1

4-1241961-7

03-I
4-1241961-7

5-1955422-7

03-G
5-1955422-7

9-1241961-7

0-2315717-6

0-2315717-7

0-2315717-6

4 POSITION VARIANTS

5 POSITION VARIANTS

0-1241959-4
0-1241817-4
2364739-4
2178571-3

2-1241959-4

4-1241959-4
2315717-4

0-1955507-4
PRELIMINARY

0-2315717-5

2-1241817-4

3-1241817-4 OBSOLETE
2322164-1
2322917-4

0-1241959-5
2364739-5

0-1241817-5

2-1241817-5

1-2178571-3

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN Kishor M 18-10-07
CHK K. Muniz 18-10-07
APVD T. Klender 18-10-07

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±0.2
4 PLC ±0.2
ANGLES FINISH

MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4

Customer Drawing

NAME STANDARD TIMER HSG. RAST 5 MARK II
Standard Timer Gehäuse RAST 5 Mark II

SIZE A1

CAGE CODE 00779

DRAWING NO. 1241961

RESTRICTED TO

SCALE 5:1

SHEET 4 OF 4

REV E4

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1241961-1](#)