





A 4x4 grid with numbers 1-6 and various symbols. The grid is as follows:


b	-	4	-	d
a	-	+	-	c
b	-	3	-	d
a	-	3	-	c
b	-	2	-	d
a	-	2	-	c
b	-	1	-	d
a	-	1	-	c

Additional symbols and connections:

- Triangle 9 is connected to the cell (1,3) containing '4'.
- Triangle 6 is connected to the cell (2,5) containing 'c'.
- Triangle 2 is connected to the cell (4,5) containing 'c'.
- Triangle 3 is connected to the cells (3,1) containing 'b' and (5,1) containing 'a'.
- Triangle 4 is connected to the cells (7,5) containing 'd' and (8,5) containing 'c'.
- A shaded square is located at the intersection of row 2 and column 5.
- A square with an 'X' is located at the intersection of row 4 and column 5.



PAY ATTENTION !
DIFFERENT LOCKING LATCHES



31 ONLY FOR 1-2178029-3, TOLERANCE IS +0.15/-0.2

4805 (3/11)

LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

- 32

ONLY FOR 2322912-3. TOLERANCE IS +0.1/-0.15
- 33

ONLY FOR 2322912-6. 1-2364737-1. TOLERANCE IS -0.30
- 34


CANDIDATE PRELIMINARY P/N. NOT YET OFFICIAL. ONLY FOR DISCUSSION. NOT YET RELEASED FOR PRODUCTION.
- 35







DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL.


	5-1241965-5	5	05-B	25	20	NATURAL	UL94-V0 & GWEPT 750 no flame 32 33	E	32 33
	1-2364737-1	11	11-B	55	50	BLUE		B	32 33
36 37	2364737-9	9	-	45	40	BLUE	UL94-V0 & GWEPT 750 no flame 32 33	C	32 33
	2364737-5	5	-	25	20	BLUE		B	32 33
	1-2364737-2	2	02-B	10	5	BLUE		B	32 33
	2364737-2	2	02-A	10	5	BLUE		B	32 33
	2322912-8	8	08-D	40	35	BLUE	PA66 UL94 V0 GWT 750	B	32 33
	2322912-6	6	06-D	30	25	BLUE		B	32 33
	2322912-3	3	-	15	10	YELLOW		B	32 33
	2-2322912-2	2	02-A	10	5	NATURE		B	32 33
	1-2322912-2	2	02-G	10	5	BLUE		B	32 33
34	2322912-2	2	02-C	10	5	GREY		B	32 33
	5-1241965-7	7	07-C	35	30	NATURAL	PA66 UL94 V0 GWT 750 CT1350	E	32 33
	4-1241965-7	7	-	35	30	NATURAL		E	32 33
36 37	5-1241965-5	5	05-B	25	20	NATURAL		E	32 33
	5-1241965-4	4	-	20	15	NATURAL		E	32 33
	4-1241965-4	4	-	20	15	NATURAL		E	32 33
34	3-1241965-4	4	-	20	15	NATURAL		E	32 33
	2-1241965-4	4	-	20	15	NATURAL		E	32 33
	1-1241965-4	4	04-C	20	15	NATURAL		E	32 33
	8-1241965-2	2	02-C	10	5	NATURAL		E	32 33
	2-1241965-2	2	-	10	5	NATURAL		E	32 33
	PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
	SPECIAL VERSION: UL94 V0 & GW T 750								

KEYING PLAN SEE SHEET 2 OF 4

2345754-1	2	02-C	10	5	NATURAL	PA66 UL94 V0	E	32 33
PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
SPECIAL VERSION: UL94 V0								

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Kishor M	18JUL2017	 TE Connectivity		
DIMENSIONS: mm		CHK K. Munz	07-NOV-06			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Th. Klenner	07-NOV-06	NAME		
		PRODUCT SPEC		2-12 POS. STANDARD TIMER HSG WITH EXTERIOR LOCKING		
MATERIAL SEE TABLES	FINISH	APPLICATION SPEC				
		WEIGHT		RESTRICTED TO		
-		-		-		
Customer Drawing			SCALE 5:1	SHEET 3 OF 4	BY B54	



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN Kishor M	18JUL2017	 TE Connectivity		
DIMENSIONS:			CHK K. Munz	07-NOV-06			
mm			APVD Th. Klenner	07-NOV-06	NAME		
			TOL. FRANCES, UNLESS OTHERWISE SPECIFIED: ±0.2		2-12 POS. STANDARD TIMER HSG WITH EXTERIOR LOCKING		
			0-PLC -0.1				
			1-PLC -0.1				
			2-PLC -0.001				
			3-PLC -0.001				
4-PLC -0.0001			PRODUCT SPEC		SIZE CASE CODE DRAWING NO. RESTRICTED TO		
108-18049			APPLICATION SPEC				
ANGLES FINISH			WEIGHT				
MATERIAL SEE TABLES			-		A1 00779 ©=1241965 -		
			Customer Drawing		SCALE 5:1 SHEET 4 of 4 REV B54		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1241965-2](#)