

CAVITY SUITABLE TO STANDARD TIMER CONTACTS
LISTED IN PROD. SPEC: I08-18049, ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte
gelistet in Prod. Spec. I08-18049, Punkt 3.3.2

1 LOCKING LATCH BETWEEN CAVITY NO.
Rasthaken zwischen Kammernummer

2 POLARIZATION RIB POSITION "a" OR POSITION "b",
AT CAVITY NO..
Polarisierungsrippen (Lage "a") oder (Lage "b")
versetzt bei Kammer Nr

3 KEYING RIB POSITION "c" OR POSITION "d",
AT CAVITY NO..
Kodierungsrippen nach unten (Lage "c") oder oben (Lage "d")
versetzt bei Kammernummer

4 AREA FOR TE LOGO ACC. TO SPEC 202-36
Bereich für TE Logo nach Spec. 202-36

5 WIDTH KEYING RIB BETWEEN CAVITY NO..
Breite Kodierrippe zwischen Kammer Nr.

6 SUITABLE TO TAB 6.3x0.8mm AND 4.8x0.8mm ACCORDING TO DIN 46244
Geegnet für Flachstecker 6.3x0.8mm und 4.8x0.8mm nach DIN 46244

7 MATING STOP BETWEEN CAVITY NO.1 AND 2, ALSO
BETWEEN THE LAST AND THE LAST BUT ONE CAVITY
Tiefenanschlag zwischen Kammer Nr.1 und 2, ebenfalls
zwischen der letzten und vorletzten Kammer

8 CONTACT CAVITY NO..
Kammernummer

9 DIMENSION A AND DIMENSION B SEE SHEET 2 OF 3
Maß A und Maß B siehe Blatt 2 von 3

10 MATED WITH TE CONNECTOR: SEE TABLE, SHEET 2 OF 3
Passender TE Gegenstecker: siehe Tabelle, Seite 2 von 3

11 GENERAL SUITABLE TAB HEADER HOUSING SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwanne, siehe RAST 5 Vorgabe

12 CONNECTION TO THE PC BOARD SEE DRAWING 88-9935-4
Leiterplattenanschluß siehe Zeichnung 88-9935-4

A B SEE TABLE, SHEET 2 OF 3
Siehe Tabelle, Blatt 2 von 3

D E

14 MATERIAL CORRESPONDS TO THE REQUIREMENT EN 60335
(INCL. GLOW WIRE TEST 750°C WITHOUT FLAME)

15 WIRE TANGLING PROTECTION

16 WIRE TANGLING PROTECTION IN COMBINATION WITH CODING RIBS,
ONLY VALID FOR VERSIONS 5-964702-3, 0-964702-3, 0-964702-1

17 KEYING ACC. TO RAST-5 STANDARD; COLOUR IS DIFFERENT

18 8 POS. SPECIAL VERSION WITH SWAGED KEYING RIB

19 SPECIAL MATERIAL PA66, UL 94 V0

20 DIMENSION "A" IS ACCEPTED WITHIN TOLERANCE +0.05/-0.20.

21 PRELIMINARY PART- NOT YET RELEASED FOR PRODUCTION

22 ONLY FOR PN 2178600-2, 3-2178600-2, 4-2178600-2, 5-2178600-2,
TOLERANCE IS +0.4 -0.2, WORST CASE CAN BE OUT OF RAST STANDARD.

23 ONLY FOR PN 2178600-2, 3-2178600-2, 4-2178600-2, 5-2178600-2,
TOLERANCE IS +0.4 -0.2

24 ONLY FOR PN 2178600-2, 3-2178600-2, 4-2178600-2, 5-2178600-2,
TOLERANCE IS $\pm 4^\circ$

25 ONLY FOR PN 3-1241965-5, 3-1241965-7 TOLERANCE IS +0.3 -0.2

26 ONLY FOR PN 3-1241965-5, 3-1241965-7 TOLERANCE IS +0.2 -0.2

27 ONLY FOR PN 3-1241965-5, 3-1241965-7 TOLERANCE IS +0.05 -0.2

28 OBSOLETE PART

29 ONLY FOR 4-1241965-7, 1-2364737-1, TOLERANCE IS -0.3

30 ONLY FOR 4-1241965-7, TOLERANCE IS +0.2/-0.25

31 ONLY FOR 1-2178029-3, TOLERANCE IS +0.15/-0.2

ADDITIONAL NOTES SEE 3 OF SHEET 4

LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

- 32

ONLY FOR 2322912-3. TOLERANCE IS +0.1/-0.15
- 33

ONLY FOR 2322912-6. 1-2364737-1. TOLERANCE IS -0.30
- 34


CANDIDATE PRELIMINARY P/N. NOT YET OFFICIAL. ONLY FOR DISCUSSION. NOT YET RELEASED FOR PRODUCTION.
- 35

DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL.

	5-1241965-5	5	05-B	25	20	NATURAL	UL94-V0 & GWEPT 750 no flame 32 33	E	32 33
	1-2364737-1	11	11-B	55	50	BLUE		B	32 33
36 37	2364737-9	9	-	45	40	BLUE	UL94-V0 & GWEPT 750 no flame 32 33	C	32 33
	2364737-5	5	-	25	20	BLUE		B	32 33
	1-2364737-2	2	02-B	10	5	BLUE		B	32 33
	2364737-2	2	02-A	10	5	BLUE		B	32 33
	2322912-8	8	08-D	40	35	BLUE	PA66 UL94 V0 GWT 750	B	32 33
	2322912-6	6	06-D	30	25	BLUE		B	32 33
	2322912-3	3	-	15	10	YELLOW		B	32 33
	2-2322912-2	2	02-A	10	5	NATURE		B	32 33
	1-2322912-2	2	02-G	10	5	BLUE		B	32 33
34	2322912-2	2	02-C	10	5	GREY		B	32 33
	5-1241965-7	7	07-C	35	30	NATURAL	PA66 UL94 V0 GWT 750 CT1350	E	32 33
	4-1241965-7	7	-	35	30	NATURAL		E	32 33
36 37	5-1241965-5	5	05-B	25	20	NATURAL		E	32 33
	5-1241965-4	4	-	20	15	NATURAL		E	32 33
	4-1241965-4	4	-	20	15	NATURAL		E	32 33
34	3-1241965-4	4	-	20	15	NATURAL		E	32 33
	2-1241965-4	4	-	20	15	NATURAL		E	32 33
	1-1241965-4	4	04-C	20	15	NATURAL		E	32 33
	8-1241965-2	2	02-C	10	5	NATURAL		E	32 33
	2-1241965-2	2	-	10	5	NATURAL		E	32 33
	PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
	SPECIAL VERSION: UL94 V0 & GW T 750								

KEYING PLAN SEE SHEET 2 OF 4

2345754-1	2	02-C	10	5	NATURAL	PA66 UL94 V0	E	32 33
PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
SPECIAL VERSION: UL94 V0								



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-928247-2](#)