



LOC		DIST		REVISIONS					
GE		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					E1	REVISED PER ECO-11-005030	26APR2011	RK	HMR

1 MATERIAL: 0.30 THICK COPPER ALLOY, PREPLATED WITH 0.0008 MINIMUM THICK REFLOW TIN OR BRIGHT TIN (ELV COMPLIANT).

ALTERNATE MATERIAL: 0.30 THICK COPPER ALLOY, PREPLATED WITH 0.0008 MINIMUM THICK BRIGHT TIN (ELV COMPLIANT).





STANDARD REELING DIRECTION




REVERSE REELING DIRECTION

4. QUALIFICATION OF THE CRIMP APPLICATION TOOLING SHALL BE CONTROLLED BY THE REQUIREMENTS ESTABLISHED UNDER USCAR 21.
5. LOOSE END SPLICING TO BE USED.



SECTION F-F



SECTION G-G

3	1326032-6 REELED FOR AMP APPLICATORS							12 AWG	I-1326032-2
	1326032-5 REELED FOR AMP APPLICATORS							14 AWG	I-1326032-1
	1326032-4 REELED FOR AMP APPLICATORS							16 AWG	I-1326032-0
	1326032-3 REELED FOR AMP APPLICATORS							18 AWG	1326032-9
	1326032-2 REELED FOR AMP APPLICATORS							20 AWG	1326032-8
	1326032-1 REELED FOR AMP APPLICATORS							22 AWG	1326032-7
2	1.35	6.8	4.30	6.09	4.7	2.70	5.25	12 AWG	1326032-6
	1.35	6.5	4.30	5.62	3.9	1.70	3.88	14 AWG	1326032-5
	1.10	5.6	3.80	4.54	3.9	1.70	3.88	16 AWG	1326032-4
	1.10	5.6	3.80	4.54	3.3	1.30	2.76	18 AWG	1326032-3
	0.90	5.0	3.40	4.11	3.3	1.30	2.76	20 AWG	1326032-2
	0.90	5.0	3.40	4.11	2.5	0.90	2.11	22 AWG	1326032-1
REELING	N	L	ØK	J	H	ØF	E	WIRE SIZE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN D. STRAUSSER 28APR99		TE Connectivity			
CHK D. BROWN 28APR99				APVD D. BROWN 28APR99		NAME			
DIMENSIONS: mm				PRODUCT SPEC		2.8mm RECEPTACLE, SEALED			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				SAE/USCAR-2 8/97		SIZE			
9 PLC ±.3				APPLICATION SPEC		CAGE CODE			
1 PLC ±0.10				114-13013		DRAWING NO			
3 PLC ±				WEIGHT		A1 00779 C=1326032			
5 PLC ±				CUSTOMER DRAWING		RESTRICTED TO			
4 PLC ±4°				SCALE		10:1			
ANGLES				SHEET		1 OF 1			
FINISH				REV		E1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1326032-3 \(Cut Strip\)](#) [1326032-3 \(Loose Piece\)](#) [1326032-3 \(Mouser Reel\)](#)