


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
K		REVISED PER ECO-20-002238	7-22-20	CT	PD



136059-2 AS SHOWN

OBSOLETE

1: WIRE INSULATION: 7.01-7.75 [.276-.305]

2: ALUMINUM WIRE CMA: 42331
WIRE: mm2: 21.4

3: THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.

19.5 GRAMS	10 or M5	11.8±0.13 [.464±.005]	5.04+/-0.13 [.198±.005]	BODY: COPPER ASTM-B187 ANNEALED TIN PLATE 0.00381[.000150] MIN THICK PER MIL-T-10727	136059-2
21 GRAMS	10 or M5	15.8+0.13/-0.26 [.622+.005/-0.010]	5.04+/-0.13 [.198+/-0.005]	INSERT & FUNNEL: BRASS ASTM B36 NICKEL PLATE SAM AMS QQ-N-290A, DATED JULY 2000,.00254 [.000100] MIN THICK	136059-1
WEIGHT	B	DIM C	DIM A	MATERIAL & FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JJ DESPRETZ 09/92	TE Connectivity		
DIMENSIONS: mm		CHK G.ROBERT 16-JAN-97			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.ROBERT 16-JAN-97	NAME		
0 PLC ± -		PRODUCT SPEC	TERMINAL, SEALED COPALUM WIRE SIZE: 4 AL		
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
2 PLC ± -		FINISH	WEIGHT 0.000000	A2 00779	C=136059
3 PLC ± -		VOIR TABLEAU	CUSTOMER DRAWING		
4 PLC ± -		VOIR TABLEAU	SCALE 2:1	SHEET 1 of 1	REV K
ANGLES ± -					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[136059-2](#)