

20


RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.
BY TYCO ELECTRONICS CORPORATION

COPYRIGHT 20

LOC	DIST	REVISIONS					
HV	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	ECO-10-022743	05NOV2010	DR	DR
			A2	ECO-11-024207	02DEC2011	DR	DR
			A3	ECO-13-012771	08AUG2013	DR	DR



SCALE 2:1

SECTION A - A

- 1 MATERIAL:
TYPE: COPPER ALLOY
2. FINISH:
UNDERPLATE TYPE: NICKEL
TOP PLATE TYPE: TIN
3. PARTS MUST BE FREE OF EXCESSIVE BURRS,
CRACKS, OR OTHER VISUAL IMPERFECTIONS
THAT MAY AFFECT FIT FORM OR FUNCTION

11.3	10.30	0.89g	A	1587723-3
10.3	9.30	0.80g	A	1587723-2
9.3	8.30	0.68g	A	1587723-1
F	E	WEIGHT	REV	PART NO

DIMENSIONS: mm		DWN D SIMPSON 02JUN2008	MATERIAL 1		FINISH	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK A TYLER 05JUN2008				
0 PLC ± 1 PLC ±0.15 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±1°		APVD J. BOLEWITZ 05JUN2008				
		PRODUCT SPEC	NAME INNER FERRULE HVA280 MULTI-CORE			
		APPLICATION SPEC				
		WEIGHT SEE TABLE	SIZE A4	CAGE CODE 00779	DRAWING NO C-1587723	RESTRICTED TO
		CUSTOMER DRAWING		SCALE 8:1	SHEET 1	OF 1
				REV A3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1587723-2](#)