

4

3

2

1

© 2021 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	ECO-13-000550	10JAN2013	DS	AT
	B3	ECO-14-000116	27FEB2014	DS	AT
	B4	ECN-21-124299	28OCT2021	SS	PK

(0.40)

(Ø E)

(11.50)

(6.00)



1 MATERIAL 1:
TYPE: COPPER ALLOY

2 MATERIAL 2:
TYPE: ALTERNATE COPPER ALLOY, NO ANNEALING

3 FINISH:
UNDERPLATE TYPE: NICKEL
TOP PLATE TYPE: TIN

4. PARTS MUST BE FREE OF BURRS, CRACKS, OR OTHER
VISUAL IMPERFECTIONS THAT MAY AFFECT FIT FORM OR FUNCTION


5 NOTE DELETED

6 PRELIMINARY PART NOT FOR PRODUCTION

6	2	5.41	6.10	7.70	SIZE C	1-1587829-3
	1	5.41	6.10	7.70	SIZE C	1587829-3
6	2	4.76	5.41	7.00	SIZE B	1-1587829-2
	1	4.76	5.41	7.00	SIZE B	1587829-2
6	2	4.11	4.76	6.40	SIZE A	1-1587829-1
	1	4.11	4.76	6.40	SIZE A	1587829-1
		MIN	MAX	E	DESCRIPTION	PART NO
		WIRE O.D.				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

- 2 1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±0.2

1 PLC ±0.10

2 PLC ±0.10

3 PLC ±0.013

4 PLC ±0.0001

ANGLES ±0.0001

FINISH

- 3

DWN
D SIMPSON
01JUN2009

CHK
A TYLER
01JUN2009

APVD
-

PRODUCT SPEC
108-2394

APPLICATION SPEC
114-13259

WEIGHT
-

TE Connectivity

NAME
OUTER FERRULE,
HVA280
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
1587829

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
B4

1470-19 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1587829-3](#)