




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M7	ADD NEW DASH NUMBER 4-3	20JUN2021	CZ	SH



8

THIS DRAWING IS UNPUBLISHED.

7

RELEASED FOR PUBLICATION

6

5

4

3

2

1

REVISIONS

P	LYR	DESCRIPTION	DATE	DWN	APVD

PART NUMBER	ROWS		POWER (L)					SIGNAL					POWER (R)						
			P10	P9	P8	P7	P6	6	5	4	3	2	1	P5	P4	P3	P2	P1	
1600636-1	D C B A		RM	RM	RM	RM	RM	E	E	E	E	E	E	RA	RA	RA	RA	RA	
5ACP + 24S + 5ACP																			

PART NUMBER	ROWS		POWER (L)		SIGNAL						POWER (R)		
			P4	P3	6	5	4	3	2	1	P2	P1	
1600636-2	D C B A		RM	RM	E	E	E	E	E	E	RA	RA	
2P + 24S + 2P													

PART NUMBER	ROWS		POWER (L)	SIGNAL						POWER (R)	
			P2	6	5	4	3	2	1	P1	
1600636-3	D C B A		RA	E	E	E	E	E	E	RA	
1P + 24S + 1P											

PART NUMBER	ROWS		POWER (L)	SIGNAL											POWER (R)			
			P4	P3	11	10	9	8	7	6	5	4	3	2	1	P2	P1	
1600636-4	D C B A		RM	RA	E	E	E	E	E	E	E	E	E	E	E	RA	RM	
2P + 44S + 2P																		

PART NUMBER	ROWS		POWER (L)				SIGNAL								POWER (R)				
			P8	P7	P6	P5	6	5	4	3	2	1	P4	P3	P2	P1			
1600636-5	D C B A		RM	RA	RM	RA	E	E	E	E	E	E	RM	RA	RM	RA			
4P + 24S + 4P																			

PART NUMBER	ROWS		POWER (L)										SIGNAL					POWER (R)							
			P16	P15	P14	P13	P12	P11	P10	P9	P8	P7	P6	P5	6	5	4	3	2	1	P4	P3	P2	P1	
1600636-6	D C B A		RA	RM	RA	RM	RA	RM	RA	RM	RA	RM	RA	RM	E	E	E	E	E	E	RA	RM	RA	RM	
4ACP + 24S + 12P																									

PART NUMBER	ROWS		POWER (L)		SIGNAL						POWER (R)				
			P6	P5	6	5	4	3	2	1	P4	P3	P2	P1	
1600636-7	D C B A		RA	RM	E	E	E	E	E	E	RM	RA	RM	RA	
4P + 24S + 2P															

PART NUMBER	ROWS		POWER (L)			SIGNAL						POWER (R)			
			P6	P5	P4	6	5	4	3	2	1	P3	P2	P1	
1-1600636-4	D C B A		RM	RM	RM	E	E	E	E	E	E	RA	RA	RA	
3ACP + 24S + 3ACP															

PART NUMBER	ROWS		POWER (L)			SIGNAL						POWER (R)			
			P6	P5	P4	6	5	4	3	2	1	P3	P2	P1	
1600636-8	D C B A		RA	RA	RA	E	E	E	E	E	E	RM	RM	RM	
3P + 16S + 3P															

PART NUMBER	ROWS		POWER (L)	SIGNAL						POWER (R)	
			P2	6	5	4	3	2	1	P1	
1600636-9	D C B A		RA	E	E	E	E	E	E	RM	
1P + 24S + 1P											

PART NUMBER	ROWS		POWER (L)	SIGNAL						POWER (R)	
			P4	P3	4	3	2	1	P2	P1	
1-1600636-0	D C B A		RA	RA	E	E	E	E	RM	RM	
2P + 16S + 2P											

PART NUMBER	ROWS		POWER (L)	SIGNAL						POWER (R)	
			P2	6	5	4	3	2	1	P1	
1-1600636-1	D C B A		RM	E	E	E	E	E	RA		
1P + 24S + 1P											

PART NUMBER	ROWS		POWER (L)	SIGNAL								POWER (R)			
			P2	6	5	4	3	2	1	P1					
1-1600636-2	D C B A		RM	RA	RM	RA	E	E	E	E	RM	RA	RM	RA	
4P + 24S + 4P															

PART NUMBER	ROWS		P(L)	SIGNAL				P(R)	
			P2	4	3	2	1	P1	
1-1600636-3	D C B A	 	RA	E	E	E	E	RM	
1P + 16S + 1P									

PART NUMBER	ROWS		POWER (L)		SIGNAL						POWER (R)				
			P6	P5	6	5	4	3	2	1	P4	P3	P2	P1	
1-1600636-4	D C B A		RM	RM	RM	E	E	E	E	E	RA	RA	RA		
3ACP + 24S + 3ACP															

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC ± °
1 PLC ± °
2 PLC ± °
3 PLC ± .005
4 PLC ± .0020
ANGLES ± °
FINISH -
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± °
1 PLC ± °
2 PLC ± °
3 PLC ± .005
4 PLC ± .0020
ANGLES ± °
FINISH -
-

DWN D. RINGLER 28JUL2003

CHK M. CORRELL 28JUL2003

APVD -

PRODUCT SPEC 108-2157

APPLICATION SPEC 114-13112

WEIGHT -

CUSTOMER DRAWING

NAME

PANEL MOUNT CABLE RECEPTACEL HOUSING WITH GUIDES MULTI-BEAM XL

SIZE A1

CAGE CODE -

DRAWING NO. 1600636

RESTRICTED TO

SCALE 4:1

SHEET 1 OF 5

REV M7

RM	STANDARD POWER CONTACT
RA	MFBL POWER CONTACT
E	SIGNAL CONTACT
CODE	DESCRIPTION
CONTACT TABLE	
TE Connectivity	
PANEL MOUNT CABLE RECEPTACEL HOUSING WITH GUIDES MULTI-BEAM XL	

4805 (3/13)

REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PART NUMBER	ROWS		POWER			SIGNAL											POWER								
			P11	P10	P9	11	10	9	8	7	6	5	4	3	2	1	P8	P7	P6	P5	P4	P3	P2	P1	
4-1600636-0	D		RM	RM	RA	E	E	E	E	E	E	E	E	E	E	E	RA	RA	RA	RM	RM	RM	RM	RA	
	E					E	E	E	E	E	E	E	E	E	E	E									
	E					E	E	E	E	E	E	E	E	E	E	E									
	E					E	E	E	E	E	E	E	E	E	E	E									
8P + 44S + 3ACP																									

PART NUMBER	ROWS		POWER		SIGNAL										POWER		
			P2		10	9	8	7	6	5	4	3	2	1	P1		
4-1600636-1	D		RM	E	E	E	E	E	E	E	E	E	E	E	RM		
	C			E	E	E	E	E	E	E	E	E	E				
	B			E	E	E	E	E	E	E	E	E	E				
	A			E	E	E	E	E	E	E	E	E	E				
1P + 40S + 1P																	

PART NUMBER	ROWS		POWER				SIGNAL			POWER				
			P8	P7	P6	P5	3	2	1	P4	P3	P2	P1	
4-1600636-2	D		RM	RM	RM	RM	E	E	E	RM	RM	RM	RM	
	C						E	E	E					
	B						E	E	E					
	A						E	E	E					
4P + 12S + 4P														

PART NUMBER	ROWS		POWER		SIGNAL			POWER		
			P4	P3	3	2	1	P2	P1	
4-1600636-3	D		RA	RA	E	E	E	RA	RA	
	C				E	E	E			
	B				E	E	E			
	A				E	E	E			
2P + 12S + 2P										

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RINGLER 28JUL2003	 TE Connectivity		
		CHK M. CORRELL 28JUL2003			
DIMENSIONS:		APVD -	NAME PANEL MOUNT CABLE RECEPTACLE HOUSING WITH GUIDES MULTI-BEAM XL	RESTRICTED TO	
	mm	PRODUCT SPEC			
		108-2157			
		APPLICATION SPEC			
		114-13112			
MATERIAL	TBD	0 P/LC ±	SIZE A 1	CAGE CODE -	
		1 P/LC ±	DRAWING NO C=1600636		
		2 P/LC ±			
		3 P/LC ± .005			
		4 P/LC ± .0020			
		ANGLES ±			
		FINISH -	WEIGHT -		
		CUSTOMER DRAWING	SCALE 4:1	SHEET 6 OF 6	REV M7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1600636-2](#)