



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H5	REVISED PER ECO-16-011163	08SEP2016	DD	AH
	H6	REVISED PER ECO-17-014752	11OCT2017	JMS	AH
	W	REVISED PER ECO-21-002133	15APR2021	SM	AH

D



- 1
- 0.00076 MINIMUM THICK GOLD PLATE OVER 0.0013 MINIMUM NICKEL PLATE.


2

3


4

C


GOLD PLATING IDENTIFIED IS ON TOP SPRING




SECTION A-A



B



SECTION B-B



SECTION C-C

2	1.2 - 2.7	AVS 0.5 - 2.0mm ² (#20 - #14 AWG)	184030-3
1	1.2 - 2.7	AVS 0.5 - 2.0mm ² (#20 - #14 AWG)	184030-1
FINISH	INSULATION DIA	WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.3

2 PLC ±0.3

3 PLC ±0.3

4 PLC ±0.3

ANGLES ±

FINISH -

DWN KD LYLE 7/07/94

CHK JP KUNKLE 7/26/94

APVD JP KUNKLE 7/26/94

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME CONTACT, RECEPTACLE, .070 TYPE

SIZE A200779

CAGE CODE C-184030

DRAWING NO

RESTRICTED TO

SCALE 10:1

SHEET 1 OF 1

REV W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[184030-3 \(Cut Strip\)](#)