



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H5	REVISED PER ECO-16-011163	08SEP2016	DD	AH
	H6	REVISED PER ECO-17-014752	10OCT2017	JMS	AH
	U	REVISED PER ECO-21-002133	15APR2021	SM	AH

D




- 1 0.00076 MINIMUM THICK GOLD PLATE OVER 0.0013 MINIMUM NICKEL PLATE.
- 2 0.0008 MINIMUM THICK PRE-TIN.
- 3 0.75 x 0.75 DIE IDENTIFICATION MARK.
- 4 FOR GOLD PLATED PART ONLY - AT LEAST ONE "G" INDICATOR MUST BE VISIBLE IN THIS LOCATION ON EITHER SIDE INDICATING GOLD PLATED CONTACT

C




SECTION A-A



SECTION C-C

B



SECTION B-B

2	1.2-2.1 (SINGLE WIRE SEALING)	AVS 0.3 - 1.00mm ²	184095-2
1	1.2-2.1 (SINGLE WIRE SEALING)	AVS 0.3 - 1.00mm ²	184095-1
FINISH	INSULATION DIA	WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KD LYLE 9/20/94		 TE Connectivity	
DIMENSIONS: mm		CHK JP KUNKLE 9/23/94			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JP KUNKLE 10/21/94		NAME CONTACT, RECEPTACLE, .070 TYPE (SCAT VERSION)
	0 PLC ±- 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC -		
	MATERIAL PHOS BRZ (0.3 THK)		APPLICATION SPEC -		
FINISH - -		WEIGHT -		DRAWING NO C=184095	
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 OF 1
				REV U	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[184095-1](#)