



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	REVISED PER ECO-13-010026	21JUN2013	DLD	CJS
	A6	REVISED PER ECO-14-015042	03OCT2014	DLD	CJS
	A7	REVISED PER ECO-15-004219	08APR2015	DLD	CJS





- ⚠ MATERIAL: BRASS
- ⚠ FINISH: PRE-PLATED WITH 0.80µm MIN TIN
- ⚠ MATERIAL ID FEATURE IN "DOWN" POSITION.
4. THE INTENDED TEMPERATURE RANGE FOR THIS TERMINAL IS -40° C TO 100° C.
- ⚠ NOT FOR SEALED APPLICATIONS.




DETAIL A
SCALE 5:1



DETAIL B
REQUIRED REELING DIRECTION
FOR TE APPLICATORS
SCALE 5:1



SECTION S-S
SCALE 20:1



SECTION N-N
SCALE 20:1

0.13mm ² = 0.85-1.05	DETAIL B	1.40	2.40	0.80	1.85	⚠	2X 0.13mm ²	1924968-8 ⚠
0.35mm ² = 1.10-1.40							0.35mm ²	
0.85-1.05	DETAIL B	0.85	1.82	0.65	1.50	⚠	26 [0.13mm ²]	1924968-7 ⚠
0.13mm ² = 0.85-1.05	DETAIL A	1.40	2.40	0.80	1.85	⚠	2X 0.13mm ²	1924968-6 ⚠
0.35mm ² = 1.10-1.40							0.35mm ²	
0.85-1.05	DETAIL A	0.85	1.82	0.65	1.50	⚠	26 [0.13mm ²]	1924968-5 ⚠
2.06 MAX	DETAIL B	1.78	2.94	1.00	1.96	⚠	18 [0.75mm ²]	1924968-4
1.50-1.85	DETAIL B	1.78	2.94	0.80	1.82	⚠	20-22 [0.5-0.35mm ²]	1924968-3
2.06 MAX	DETAIL A	1.78	2.94	1.00	1.96	⚠	18 [0.75mm ²]	1924968-2
1.50-1.85	DETAIL A	1.78	2.94	0.80	1.82	⚠	20-22 [0.5-0.35mm ²]	1924968-1
INSULATION DIAMETER	REELING	M	L	K	J	FINISH	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3
1 PLC ±0.3
2 PLC ±0.15
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

MATERIAL

⚠

DWN H. MOLL 02OCT2008
CHK J. HALL 02OCT2008
APVD J. HALL 02OCT2008

PRODUCT SPEC

108-2296-1

APPLICATION SPEC

114-13183

WEIGHT

-

CUSTOMER DRAWING

NAME

CONTACT, MALE, 0.64mm, GENERATION Y

SIZE A1

CAGE CODE 00779

DRAWING NO. 1924968

RESTRICTED TO

-

SCALE 10:1

SHEET 1

OF 1

REV A7

TE Connectivity

CONTACT, MALE, 0.64mm, GENERATION Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1924968-7](#)