



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL CREATED	30MAR2021	CL	WH



- NOTES:
- MATERIAL AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702
 - MATERIAL CHARACTERISTIC
SMA CONN: INNER CONTACT: BeCu, 30MICRO-INCH MIN GOLD PLATING
OUTER BODY: STAINLESS STEEL, PASSIVATION
OTHER: BRASS
CABLE: 0.047" FLEXIBLE CABLE, BLUE
 - PRODUCT RATING:
TEMPERATURE: -45°C TO +125°C
VOLTAGE: 500V (RMS)
CHARACTERISTIC IMPEDANCE: 50 OHMS (NORMAL)
FREQUENCY RANGE: DC TO 27GHz
BEND RADIUS: 5MM MIN (REPEATED)
 - CABLE ASSEMBLY TO BE 100% SI TESTED
VSWR: 1.25:1 MAX @ DC~27000MHz
INSERT LOSS: $\{[0.033 * \text{SQRT}(f) + 0.000039 * f] * \text{LENGTH} + 0.015f / 1000\}$ dB (TYPICAL)
LENGTH UNIT IS METER IN THE FORMULA. f IS FREQUENCY IN MHz
 - CONNECTOR FOLLOW IEC 60169-15
 - CABLE ASSEMBLY CAN MEET MECHANICAL
COUPLING TORQUE(NORMAL): 0.8~1.1N.M
TENSILE STRENGTH OF COUPLING: 180N MIN
CABLE PULLING: 50N MIN
 - LABEL WILL MARK PN, NAME, YEAR AND WEEK
 - CONNECTOR BE PROTECTED WITH CAP

2-2016753-0	2000±10
1-2016753-5	1500±10
1-2016753-0	1000±10
2016753-9	350±5
2016753-8	250±3
2016753-7	150±3
2016753-6	50±3
2016753-5	500±5
2016753-4	400±5
2016753-3	300±4
2016753-2	200±3
2016753-1	100±3
PART NUMBER	LENGTH

PC	1	LABEL	4
MR	AR	HEAT SHRINK TUBE BLACK	3
MR	AR	CABLE EPC-047, 27GHz, FLEX, BLUE	2
PC	2	SMA PLUG, 27GHz, FOR EPC-047	1
UNIT	Q'TY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 23DEC2020 Cedar Liu		
		CHK 23DEC2020 Roger Song		
DIMENSIONS: mm		APVD Wenke He	NAME EP-SMA, 27GHz STRAIGHT MALE-MALE WITH EPC-047 FLEXIBLE	
		PRODUCT SPEC		
		APPLICATION SPEC		
MATERIAL TBD		WEIGHT	SIZE A3	CAGE CODE 00779
		FINISH finish_spec_2	DRAWING NO C-2016753	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1
			REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2016753-7](#)