




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECR-21-006029	02SEP2021	VG	PO

SPECIFICATIONS

CONTACT RATING: SILVER: 3A @ 250 VAC RESISTIVE
GOLD: 0.4VA @ 20VDC OR PEAK AC
INSULATION RESISTANCE: 1,000MΩ MIN AT 500VDC
DIELECTRIC STRENGTH: 2,000V RMS @ SEA LEVEL
CONTACT RESISTANCE: 50 mΩ MAX @ 1A 12VDC (INITIAL VALUE)
ELECTRICAL LIFECYCLES: 50,000 MAKE AND BREAK CYCLES
AT FULL LOAD

ACTUATION FORCE: SP: 2.5±1 NEWTON, DP: 3.5±1 NEWTON
ACTUATION TRAVEL: 3.2mm
SEALED PER IP67, IK10 (STAINLESS)
OPERATING TEMPERATURE: -20°C TO +55°C
MECHANICAL LIFECYCLES: MOMENTARY: 1,000,000 CYCLES
LOCKING: 500,000 CYCLES
HARDWARE TORQUE: 5-14 N-m





MATERIALS

BUSHING: STAINLESS STEEL
BASE: PBT (UL 94-V0), PC (UL 94-V2)
ACTUATOR: STAINLESS STEEL, PC
SEALING: O-RING (SILICONE)
TERMINAL/CONTACT: COPPER BASE, SILVER/GOLD PLATED
HEX NUT: BRASS BASE, NICKEL PLATED



1 ALL MATERIAL AND FINISHES SHALL COMPLY WITH EU DIRECTIVE
2002/95/EC OF 27JAN2003 (ROHS)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 08FEB2016	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK HILL RYAN 08FEB2016			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HILL RYAN 08FEB2016	NAME ANTI-VANDAL SWITCH 19mm MOVING RING LED		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC	SIZE A2		
MATERIAL -		WEIGHT 0	CAGE CODE 00779		
FINISH -		CUSTOMER DRAWING	DRAWING NO C-2213767		
		SCALE 1:1	SHEET 1 OF 4		
			REV B1		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




ASSEMBLED VIEW



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 08FEB2016	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL RYAN 08FEB2016				
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		ANTI-VANDAL SWITCH 19mm			
	1 PLC ± -		MOVING RING LED			
	2 PLC ± -		SIZE			
3 PLC ± -		APVD HILL RYAN 08FEB2016	CAGE CODE		DRAWING NO	RESTRICTED TO
4 PLC ± -		PRODUCT SPEC	A2 00779		C=2213767	-
ANGLES ± -		APPLICATION SPEC	SCALE		SHEET	REV
FINISH		WEIGHT	1:1		2 OF 4	B1
MATERIAL		CUSTOMER DRAWING				

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		-		-	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.					
				REVISIONS			
P	LTR	DESCRIPTION			DATE	DWN	APVD
	-	SEE SHEET 1			-	-	-
SINGLE POLE- LOCKING		GOLD	BLUE	24V	AV1911E724R04	4-2213767-0	
		SILVER	BLUE	24V	AV1911E724Q04	3-2213767-9	
		GOLD	BLUE	12V	AV1911E712R04	3-2213767-8	
		SILVER	BLUE	12V	AV1911E712Q04	3-2213767-7	
		GOLD	GREEN	24V	AV1911E624R04	3-2213767-6	
		SILVER	GREEN	24V	AV1911E624Q04	3-2213767-5	
		GOLD	GREEN	12V	AV1911E612R04	3-2213767-4	
		SILVER	GREEN	12V	AV1911E612Q04	3-2213767-3	
		GOLD	YELLOW	24V	AV1911E524R04	3-2213767-2	
		SILVER	YELLOW	24V	AV1911E524Q04	3-2213767-1	
		GOLD	YELLOW	12V	AV1911E512R04	3-2213767-0	
		SILVER	YELLOW	12V	AV1911E512Q04	2-2213767-9	
		GOLD	RED	24V	AV1911E324R04	2-2213767-8	
		SILVER	RED	24V	AV1911E324Q04	2-2213767-7	
		GOLD	RED	12V	AV1911E312R04	2-2213767-6	
		SILVER	RED	12V	AV1911E312Q04	2-2213767-5	
		GOLD	WHITE	24V	AV1911E124R04	2-2213767-4	
		SILVER	WHITE	24V	AV1911E124Q04	2-2213767-3	
		GOLD	WHITE	12V	AV1911E112R04	2-2213767-2	
		SILVER	WHITE	12V	AV1911E112Q04	2-2213767-1	
SINGLE POLE- MOMENTARY		GOLD	BLUE	24V	AV1910E724R04	2-2213767-0	
		SILVER	BLUE	24V	AV1910E724Q04	1-2213767-9	
		GOLD	BLUE	12V	AV1910E712R04	1-2213767-8	
		SILVER	BLUE	12V	AV1910E712Q04	1-2213767-7	
		GOLD	GREEN	24V	AV1910E624R04	1-2213767-6	
		SILVER	GREEN	24V	AV1910E624Q04	1-2213767-5	
		GOLD	GREEN	12V	AV1910E612R04	1-2213767-4	
		SILVER	GREEN	12V	AV1910E612Q04	1-2213767-3	
		GOLD	YELLOW	24V	AV1910E524R04	1-2213767-2	
		SILVER	YELLOW	24V	AV1910E524Q04	1-2213767-1	
		GOLD	YELLOW	12V	AV1910E512R04	1-2213767-0	
		SILVER	YELLOW	12V	AV1910E512Q04	2213767-9	
		GOLD	RED	24V	AV1910E324R04	2213767-8	
		SILVER	RED	24V	AV1910E324Q04	2213767-7	
		GOLD	RED	12V	AV1910E312R04	2213767-6	
		SILVER	RED	12V	AV1910E312Q04	2213767-5	
		GOLD	WHITE	24V	AV1910E124R04	2213767-4	
		SILVER	WHITE	24V	AV1910E124Q04	2213767-3	
		GOLD	WHITE	12V	AV1910E112R04	2213767-2	
		SILVER	WHITE	12V	AV1910E112Q04	2213767-1	
POLE/THROW		CONTACT	LED COLOR	LED VOLTAGE	TE DESCRIPTIVE PN		TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08FEB2016 NAGALAKSHMI K		 TE Connectivity									
DIMENSIONS: mm [INCHES]		CHK 08FEB2016 HILL RYAN											
		APVD 08FEB2016 HILL RYAN		NAME ANTI-VANDAL SWITCH 19mm MOVING RING LED									
		PRODUCT SPEC											
		APPLICATION SPEC											
		-											
MATERIAL -		FINISH -		WEIGHT -		SIZE A2		CAGE CODE 00779		DRAWING NO C=2213767		RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 1:1		SHEET 3 of 4		REV B1			

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

DOUBLE POLE-LOCKING

DOUBLE POLE-MOMENTARY

POLE/THROW

GOLD	BLUE	24V	AV1921E724R04	8-2213767-0
SILVER	BLUE	24V	AV1921E724Q04	7-2213767-9
GOLD	BLUE	12V	AV1921E712R04	7-2213767-8
SILVER	BLUE	12V	AV1921E712Q04	7-2213767-7
GOLD	GREEN	24V	AV1921E624R04	7-2213767-6
SILVER	GREEN	24V	AV1921E624Q04	7-2213767-5
GOLD	GREEN	12V	AV1921E612R04	7-2213767-4
SILVER	GREEN	12V	AV1921E612Q04	7-2213767-3
GOLD	YELLOW	24V	AV1921E524R04	7-2213767-2
SILVER	YELLOW	24V	AV1921E524Q04	7-2213767-1
GOLD	YELLOW	12V	AV1921E512R04	7-2213767-0
SILVER	YELLOW	12V	AV1921E512Q04	6-2213767-9
GOLD	RED	24V	AV1921E324R04	6-2213767-8
SILVER	RED	24V	AV1921E324Q04	6-2213767-7
GOLD	RED	12V	AV1921E312R04	6-2213767-6
SILVER	RED	12V	AV1921E312Q04	6-2213767-5
GOLD	WHITE	24V	AV1921E124R04	6-2213767-4
SILVER	WHITE	24V	AV1921E124Q04	6-2213767-3
GOLD	WHITE	12V	AV1921E112R04	6-2213767-2
SILVER	WHITE	12V	AV1921E112Q04	6-2213767-1
GOLD	BLUE	24V	AV1920E724R04	6-2213767-0
SILVER	BLUE	24V	AV1920E724Q04	5-2213767-9
GOLD	BLUE	12V	AV1920E712R04	5-2213767-8
SILVER	BLUE	12V	AV1920E712Q04	5-2213767-7
GOLD	GREEN	24V	AV1920E624R04	5-2213767-6
SILVER	GREEN	24V	AV1920E624Q04	5-2213767-5
GOLD	GREEN	12V	AV1920E612R04	5-2213767-4
SILVER	GREEN	12V	AV1920E612Q04	5-2213767-3
GOLD	YELLOW	24V	AV1920E524R04	5-2213767-2
SILVER	YELLOW	24V	AV1920E524Q04	5-2213767-1
GOLD	YELLOW	12V	AV1920E512R04	5-2213767-0
SILVER	YELLOW	12V	AV1920E512Q04	4-2213767-9
GOLD	RED	24V	AV1920E324R04	4-2213767-8
SILVER	RED	24V	AV1920E324Q04	4-2213767-7
GOLD	RED	12V	AV1920E312R04	4-2213767-6
SILVER	RED	12V	AV1920E312Q04	4-2213767-5
GOLD	WHITE	24V	AV1920E124R04	4-2213767-4
SILVER	WHITE	24V	AV1920E124Q04	4-2213767-3
GOLD	WHITE	12V	AV1920E112R04	4-2213767-2
SILVER	WHITE	12V	AV1920E112Q04	4-2213767-1
CONTACT	LED COLOR	LED VOLTAGE	TE DESCRIPTIVE PN	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0

1

2

3

4

PLC
PLC
PLC
PLC
PLC

±
±
±
±
±

-
-
-
-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

-

DWN
NAGALAKSHMI K

CHK
HILL RYAN

APVD
HILL RYAN

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

08FEB2016

08FEB2016

08FEB2016

TE Connectivity

ANTI-VANDAL SWITCH 19mm MOVING RING LED

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2213767

RESTRICTED TO

SCALE
1:1

SHEET
4 OF 4

REV
B1

1471-9 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2213767-1](#)