



STANDARD FASTON TERMINAL LINE

Quick Reference Guide

PRODUCT DESCRIPTION

TE Connectivity's (TE) FASTON products have been the industry leader in the appliance and automotive industries for years. TE continues to reinvent the FASTON product line to meet the changing trends in these and other industries. We have seen the need for lower insertion forces, higher performance and higher temperature ratings within the FASTON product family, so TE is proud to introduce several new products specifically designed to meet these requirements. These new products come with the same strong engineering support and high quality that TE has provided for over 60 years.

NEW STANDARD LINE

The new Standard line of FASTON terminals includes high temperature nickel plated steel receptacles and tin plated brass receptacles utilizing our F-Crimp, Tab-Lok and the new 2D crimp technology. The Standard line of FASTON receptacles is easily identifiable by the dogbone shaped front end of the receptacle allowing the mating tab to mate on a rolled edge instead of a sheared edge for reduced insertion force. The new Standard tin plated brass receptacles are UL rated to 125°C versus our legacy tin plated brass FASTON receptacles rated at only 110°C. Finally, our Standard tin plated brass receptacles are performance tested on the 6th mating cycle instead of the 1st mating cycle, to allow for disconnection and reconnection during service calls without needing to replace the receptacles. All Standard line FASTON receptacles are backward compatible with our existing FASTON housings.

Our Standard line 2D crimp FASTON receptacles will allow customers to standardize on four receptacles to cover their full wire range allowing them to replace hundreds of other receptacles, potentially giving them better productivity and pricing while reducing change-overs.

Fewer receptacles require less application tooling and improves inventory handling. The wide range wire crimps can easily accommodate under-sized wire being used more often in production today.

Nickel plated steel receptacles in the Standard line of FASTON terminals are specifically designed for high temperature applications. They are UL rated to 250°C.

KEY FEATURES

- Lower insertion forces
- Higher performance
- Higher temperature ratings
- 2D crimp style terminal available

STANDARD FASTON TERMINAL LINE

Quick Reference Guide

STANDARD FASTON RECEPTACLES WITH F CRIMP OR TAB-LOK

TIN PLATED BRASS, RATED 125°C

Part Number	Mating Tab	Wire AWG	Orientation	Crimp	Applicator	Recommended 1P Housing
2238196-3	250x032	18-14	Straight	F Crimp	2150016	480416-1
2238204-3	250x032	22-18	Straight	F Crimp	2150030-2	480416-1
2238197-3	250x032	18-12	RH Flag	Tab-Lok	1852633-1 / 687395-6	1969507-2
2238205-3	250x032	22-18	RH Flag	Tab-Lok	567372-2	1969507-2
2238206-3	250x032	16+14, 2x14 or 2x16	RH Flag	Tab-Lok	1385580-2	1969507-2
2375768-3	250X32	16-12	RH Flag	F Crimp	4150076	1969657-1
2384879-3	250X32	22-18	RH Flag	F Crimp	4150106-2	1969657-1
2375767-3	250X32	16-12	LH Flag	F Crimp	4150075	1969656-1
2384863-3	250X32	22-18	LH Flag	F Crimp	4150105-2	1969656-1
2238207-3	187x020	20-16	Straight	F Crimp	2150007-2	480435-1
2238198-3	187x032	20-16	Straight	F Crimp	2150007	480435-1
2238199-3	187x032	18-16 or 2x18	Straight	F Crimp	2150055	480435-1
2238200-3	187x032	20-16	RH Flag	Tab-Lok	687392-9 / 687392-7	-



STANDARD FASTON RECEPTACLES WITH 2D CRIMP

TIN PLATED BRASS, RATED 125°C

Part Number	Mating Tab	Wire AWG	Orientation	Crimp	Applicator	Recommended 1P Housing
2238173-3	250x032	22-12	Straight	2D Crimp	2150831-2	480416-1
2238171-3	250x032	22-12	RH Flag	2D Crimp	2150829-2	1969657-1
2238209-3	250x032	22-12	LH Flag	2D Crimp	4150013-2	1969656-1
2238174-3	187x032	24-14	Straight	2D Crimp	2150832-2	2-480435-2
2238172-3	187x032	24-14	RH Flag	2D Crimp	2150830-2	-



MEASUREMENT TOOL ANVIL ASSEMBLY NEEDED TO CHECK CRIMP HEIGHT OF 2D CRIMP TERMINALS: 2844999-1


STANDARD FASTON TERMINAL LINE

Quick Reference Guide

STANDARD FASTON RECEPTACLES

HIGH TEMPERATURE NICKEL PLATED STEEL, RATED 250°C

Part Number	Mating Tab	Wire AWG	Orientation	Crimp	Applicator	Recommended 1P Housings
1742198-1	250x032	18-14	Straight	F Crimp	2150016	1969632-1 (200°C)
2238143-1	250x032	22-18	Straight	F Crimp	2150086	1969632-1 (200°C)
1742543-1	250x032	18-12	RH Flag	Tab-Lok	1852633-1 / 687395-6	1969507-2 (150°C)
2238142-1	250x032	22-18	RH Flag	Tab-Lok	567372-2	1969507-2 (150°C)
1742626-1	250x032	16+14, 2x14 or 2x16	RH Flag	Tab-Lok	1385580-1 / 1852646-1	1969507-2 (150°C)
1742841-1-1	187x020	20-16	Straight	F Crimp	2150007	2-480435-3 (200°C)
						2-480435-2 (150°C)
1742883-1	187x020	20-16	Straight	F Crimp	2150007	2-480435-3 (200°C)
						2-480435-2 (150°C)
1742899-1	187x020	18-16 or 2x18	Straight	F Crimp	2150055	2-480435-3 (200°C)
						2-480435-2 (150°C)
2238041-1	187x020	20-16	RH Flag	Tab-Lok	687392	-



te.com

FASTON, TE, TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity Ltd. family of companies All Rights Reserved

1-1773948-2 12/21 Revised

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2238174-3](#)