





REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
	B	REVISED PER ECO-17-018523	22JAN2018	PHM



FLAT HEAD SCREWS	STEEL OR STAINLESS STEEL	STAINLESS STEEL OR PASSIVATED	--
SIZE 22 STAMPED AND FORMED SOCKET CONTACTS QTY = 120	BODY: COPPER ALLOY HOOD: STAINLESS STEEL	BODY: .000050 [0.00127] MIN GOLD ON MATING TINES, SnPb ON TAIL, BOTH OVER NICKEL PLATE HOOD: PASSIVATED	ONE PIECE DESIGN WITH NON-REMOVABLE CONTACTS
60 POSITION INSERT 2 PLC	THERMOPLASTIC	NONE	ONE PIECE DESIGN WITH NON-REMOVABLE CONTACTS
5C2 INSERT	THERMOPLASTIC	NONE	--
POLARIZATION KEYWAY	ZINC ALLOY PER ASTM-B-86	--	--
KEYWAY RETAINER PLATE	ALUMINUM ALLOY	BLUE ANODIZED PER MIL-A-8625	--
SHELL	ALUMINUM ALLOY PER ASTM-B-85	CHROMATE CONVERSION PER MIL-C-5541, TYPE II, CLASS 3	--
RETENTION PLATES COMPONENT	ALUMINUM ALLOY PER ASTM-B-209	FINISH	REMARKS

- 1 ASSEMBLED CONNECTOR FEATURES COMPLY WITH ARINC 600 SPECIFICATION EXCEPT AS NOTED.
- 2 TE PART NO. AND DATE CODE MARKED IN THIS AREA.
3. KEYING INSTALLED IN POSITION "01".
4. CONNECTOR IS SUPPLIED WITH A DUST COVER INSTALLED FOR SHIPPING.
5. MODULE A:  
NON-REMOVABLE SIZE 22 POSTED SOCKET CONTACTS, QTY = 60  
MODULE B:  
NON-REMOVABLE SIZE 22 POSTED SOCKET CONTACTS, QTY = 60  
MODULE C:  
NO CONTACTS

"01"	2293024-1
KEYING POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 6-22-15	TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK W. BERNHART 6-22-15		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W. BERNHART 6-22-15	NAME RCPT ASSY, SZ 1, ARINC 600 (60/60/5C2) WITH SIZE 22 STAMPED AND FORMED CONTACTS	
0 PLC ±.005 (0.13)		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
1 PLC ±.005 (0.13)		APPLICATION SPEC	RESTRICTED TO	
2 PLC ±.005 (0.13)		WEIGHT	A100779C=2293024	
3 PLC ±.005 (0.13)		CUSTOMER DRAWING	SCALE 3:2 SHEET 1 OF 1 REV B	
4 PLC ±.005 (0.13)				
ANGLES				
FINISH				
MATERIAL SEE TABLE				
SEE TABLE				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2293024-1](#)