




ELCON MICRO WIRE-TO-BOARD POWER SOLUTIONS

TE Connectivity's (TE) ELCON Micro wire-to-board power solutions can provide a high current up to 12.5A per pin in the common industry footprint of 3.0mm. This current density in a compact design is useful for servers, switches, storage devices and testing machines. A standard industry footprint of connectors and plug kits allows for easy upgrades to existing designs and makes our headers PCB footprint compatible with other suppliers. Custom cable assemblies help complete our high current portfolio allowing design flexibility.

Benefits

- High current density up to 12.5A per pin maximum in the common industry footprint of 3.0mm (contact pitch)
- Common industry footprint allows for easy upgrades to existing designs
- Support 2 to 24 pin configurations and different currents with multiple combinations of different wire sizes
- PCB footprint compatible with other suppliers
- Easy assembly with virtually fool-proof mating features
- Perform reliably in harsh environments with maximum operating temperature of 105°C
- Made with halogen-free material
- Low contact resistance of 5mΩ max provides lower temperature rise and lower power loss
- Plug kits and custom cable assemblies help complete our high current portfolio allowing design flexibility

Image	Description	TE Part Number
	Vertical header, 4 position	1-2204801-8
	Vertical header, 8 position	3-2204801-8
	Vertical header, 16 position	7-2204801-8
	Cable terminal, Tin Plate	1-2204749-8
	Cable housing, 4 position	2204748-2
	Cable housing, 8 position	2204748-4
	Cable housing, 16 position	2204748-8
	Cable Assembly 2x4	2354120-1
	Cable Assembly 2x6	2354149-1
	Cable Assembly 2x8	2354173-1

Applications

- Servers
- Switch/Routers
- Power supplies and distribution
- Gaming Machines
- Printers
- Security Systems
- Business retail equipment (BRE)
- Dryers
- Refrigerator
- Test Equipment
- Measurement Equipment
- Diagnostic equipment
- Patient Monitor

Materials

- Contacts: Copper alloy, tin plating
- Housing: thermo plastic, UL 94-V0
- Halogen-free

Ratings

- Voltage rating: 600V max AC or DC
- Current rating: 12.5A max per contact
- Contact resistance: 5mΩ max
- Temperature rating: -40°C to 105°C

Specifications

- Product specs: 108-128068
- Qualification test report: 501-128069

te.com

ELCON, TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2019 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773956-2 07/19 DND

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2204801-8](#)