



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECO-21-006709	18JUN2021	RK	AS

SINGLE POLE SWITCH WITH DUAL COLOR LED's AND FLYING LEADS



ASSEMBLED VIEW

1471-9 (1/15)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHIVAKUMAR S S 15MAR2017	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK SANJAY SHINDIKAR 15FEB2017		
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD SANJAY SHINDIKAR 15FEB2017	NAME ANTI-VANDAL SWITCH 25mm, MOVING RING LED AND FLYING LEADS	
0 PLC ± - 1 PLC ± 0.4 [.016] 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC APPLICATION SPEC	SIZE A2	
MATERIAL -		WEIGHT 0	CAGE CODE 00779	
FINISH -		CUSTOMER DRAWING	DRAWING NO C-2317657	
		SCALE 1:1	SHEET 1 OF 3	
			REV A1	

2317657



2317657



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

DOUBLE POLE SWITCH WITH DUAL COLOR LED's AND FLYING LEADS



ASSEMBLED VIEW



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 15MAR2017 SHIVAKUMAR S S		 TE Connectivity							
		CHK 15FEB2017 SANJAY SHINDIKAR									
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ANTI-VANDAL SWITCH 25mm, MOVING RING LED AND FLYING LEADS —							
		APVD 15FEB2017 SANJAY SHINDIKAR									
		PRODUCT SPEC —									
		APPLICATION SPEC —									
MATERIAL —		FINISH —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
		WEIGHT 0		A2	00779	C=2317657	—				
CUSTOMER DRAWING						SCALE	1:1	SHEET	2 of 3	REV	A1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- - -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

SPECIFICATION:



CONTACT RATING: SILVER; 3A @ 250VAC RESISTIVE
GOLD; 0.4A @ 20VDC OR PEAK AC
INSULATION RESISTANCE: 1,000MΩ MIN AT 500VDC
DIELECTRIC STRENGTH: 2,000V RMS @ SEA LEVEL
CONTACT RESISTANCE: 50mΩ MAX @ 1A 12VDC (INITIAL VALUE), SOLDER TERMINALS
100mΩ MAX @ 1A 12VDC (INITIAL VALUES), FLYING LEADS.
ELECTRICAL LIFE CYCLES: 50,000 MAKE AND BREAK CYCLES AT FULL LOAD.
ACTUATION FORCE: SP: 2.5±1 N, DP: 3.5±1 N
ACTUATION TRAVEL: APPROXIMATELY 3.2mm
SEALED PER IP67, IK08
OPERATING TEMPERATURE: -20°C TO +55°C
MECHANICAL LIFE CYCLES: MOMENTARY; 1,000,000 CYCLES
LOCKING; 500,000 CYCLES
HARDWARE TORQUE: 5-14 N-m.

MATERIALS

BUSHING: STAINLESS STEEL,
BASE: PBT (UL 94-V0), PC (UL 94-V2),
ACTUATOR: STAINLESS STEEL, PC
O-RING: SILICONE
TERMINAL/CONTACT: COPPER BASE, SILVER/GOLD PLATED,
HEX NUT: BRASS BASE, NICKEL PLATED,
WIRE:UL3385.
INNER ASSEMBLY: POM/PA66
SPRING: SPRING STEEL
SEALING: SILICONE

1. ALL MATERIAL AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003(ROHS).

SILVER	MOVING RING	FLYING LEADS TERMINALS	DOUBLE POLE – MOMENTARY	RED & BLUE	24	AV2520EB24T5Q04	1-2317657-2
				RED & BLUE	12	AV2520EB12T5Q04	1-2317657-1
				RED & GREEN	24	AV2520EA24T5Q04	1-2317657-0
				RED & GREEN	12	AV2520EA12T5Q04	2317657-9
			SINGLE POLE – LOCKING	RED & BLUE	24	AV2511EB24T5Q04	2317657-8
				RED & BLUE	12	AV2511EB12T5Q04	2317657-7
				RED & GREEN	24	AV2511EA24T5Q04	2317657-6
				RED & GREEN	12	AV2511EA12T5Q04	2317657-5
			SINGLE POLE – MOMENTARY	RED & BLUE	24	AV2510EB24T5Q04	2317657-4
				RED & BLUE	12	AV2510EB12T5Q04	2317657-3
				RED & GREEN	24	AV2510EA24T5Q04	2317657-2
				RED & GREEN	12	AV2510EA12T5Q04	2317657-1
CONTACT FINISH	LIGHT TYPE	TERMINAL OPTION	POLE/THROW	LED COLOR	LED VOLTAGE	TE DESCRIPTIVE PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 15MAR2017 SHIVAKUMAR S S CHK 15FEB2017 SANJAY SHINDIKAR APVD 15FEB2017 SANJAY SHINDIKAR		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ANTI-VANDAL SWITCH 25mm, MOVING RING LED AND FLYING LEADS	
		0 PLC ± - 1 PLC ± 0.4[.016] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 2°			
MATERIAL -		FINISH -			
		PRODUCT SPEC -		SIZE A2	
		APPLICATION SPEC -			
		WEIGHT 0		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C=2317657	
				RESTRICTED TO -	
				SCALE 1:1	
				SHEET 3 of 3	
				REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2317657-0](#)