




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECO-20-002055	14FEB2020	AP	GF
C		REVISED PER ECO-21-005292	01MAY2021	KK	AK

△ LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -4): -1 SHOWN.

STE 2334985-1 X

0.5M - 32AWG

PPPPPLYWWSSS

00000000000000000000

TE LOGO, TE P/N, X= MFG LOCATION

LENGTH - CABLE GAGE

PN, MANUFACTURING LOCATION AND DATE CODE SERIAL NUMBER

BAR CODE

2. SEE SHEET 2 FOR WIRING SCHEMATIC.
3. ALL MATERIALS, COMPONENTS AND PROCESS SHALL COMPLY WITH TEC-138-702. (CONTAINS NO BANNED OR RESTRICTED SUBSTANCES).
4. CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.
5. NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702

△ TEST IN ACCORDANCE WITH IEEE802.3by.

△ LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -43): -41 SHOWN

STE 4-2334985-1 X

0.5M - 32AWG

PPPPPLYWWSSS

00000000000000000000

TE LOGO, TE P/N, X= MFG LOCATION

LENGTH - CABLE GAGE

PN, MANUFACTURING LOCATION AND DATE CODE SERIAL NUMBER


BAR CODE

△ DASH NUMBER 41 THRU 43 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

△ 8	32 AWG	1500 +50/-0	4-2334985-3
	32 AWG	1000 +50/-0	4-2334985-2
	32 AWG	500 +50/-0	4-2334985-1
△ 6	32 AWG	2000 +80/-0	2334985-4
	32 AWG	1500 +50/-0	2334985-3
	32 AWG	1000 +50/-0	2334985-2
	32 AWG	500 +50/-0	2334985-1
STANDARD	WIRE GAGE	L	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M_Y1 03MAY2018	STE TE Connectivity	
DIMENSIONS:		CHK M_Y1 03MAY2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M_Y1 03MAY2018	NAME	
		CHK M_Y1 03MAY2018	CABLE ASSEMBLY, SFP+ TO SFP+, 28G	
	0 PLC ±°	PRODUCT SPEC	SIZE	
			A1	
	1 PLC ±°	APPLICATION SPEC	CAGE CODE	
			00779	
	2 PLC ±°	WEIGHT	DRAWING NO	
			2334985	
	3 PLC ±°	CUSTOMER DRAWING	RESTRICTED TO	
			C	
	4 PLC ±°	SCALE	SHEET	
			1 OF 2	
MATERIAL	FINISH	SCALE	REV	
-	-	2:1	C	
-	-			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M_Y1	03MAY2018		 TE Connectivity	
		CHK G.FRANKLIN	03MAY2018			
DIMENSIONS:		APVD G.FRANKLIN		03MAY2018		NAME CABLE ASSEMBLY, SFP+ TO SFP+, 28G 32 AWG
mm		PRODUCT SPEC				
		-				SIZE A1
		APPLICATION SPEC				
		WEIGHT				
		CUSTOMER DRAWING				
MATERIAL		FINISH		RESTRICTED TO		
-		-		SCALE 2:1		
-		-		SHEET 2 OF 2		
				REV C		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2334985-1](#)