





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	05MAR2020	X.L	I.Y
	A1	SEE ECR-21-000027	04 JAN2021	L.G	I.Y
	B	SEE ECR-21-002821	16MAR2021	L.G	I.Y
	B1	ECN-21-127853	24NOV2021	L.G	Z.Z



1. THIS TAB HOUSING MATES WITH PLUG ASSEMBLY PN 2366494-X,
(X=1, 2, 3, 4 FOR VARIOUS CODE).
2. FOR FLANGE VERSION, NEED MATE WITH FIX RING PN 2366517-X
RECOMMENDED WALL INTERFACE SEE CUSTOMER DRAWING 2366517
3. MATERIAL SEE TABLE
4. DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS(20=2020)
MONTH: THIRD DIGIT , EXCLUDING 1 , A=JAN, B=FEB, C=MARCH...(K=OCTOBER)
DAY: FOURTH AND FIFTH DIGITS(14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS(11=11AM)
5. IDENTIFICATION FOR CABLE PINOUT.
6. TPA SEATED ON PRE-LOCK POSITION FOR DELIVERY.
7. PULL TPA TO PRE-LOCK BEFORE TERMINAL INSERTION IN CASE OF TPA BEING H
TO END-LOCK POSITION.
8. REFER TO 114-151001 FOR DT SIZE 16 TERMINAL APPLICATION SPECIFICATION.
REFER TO 114-151003 FOR DT SIZE 20 TERMINAL APPLICATION SPECIFICATION.
APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZE:




TERMINAL PN	WIRE SIZE (MM2)	INSULATION WIRE (MM2)	PIOUT NUMBER
16#	1.0-2.5	Ø1.9-Ø3.0	1,8,9,16,33,40,41,48
20#	0.5-1.5	Ø1.4-Ø2.4	OTHER PINS

9. LASER PRODUCT PN. SUCH AS "--1" MEANS 2366509-1, "2--1" MEANS 2-2366509-1.
10. REFER TO DRAWING 2373921 FOR APPLICABLE PART NO. OF SEALING PLUG.

1	-	-	-	BLUE	PBT-GF30	REAR CAP	4	
-	1	-	-	GREEN				
-	-	1	-	GREY				
-	-	-	1	BLACK				
1	1	1	1	RUST RED	VMQ	GROMMET	3	
1	-	-	-	BLUE	PBT-GF30	HOUSING CODING D	2	
-	1	-	-	GREEN		HOUSING CODING C		
-	-	1	-	GREY		HOUSING CODING B		
-	-	-	1	BLACK		HOUSING CODING A		
1	1	1	1	YELLOW	PBT-GF30	TPA	1	
QTY. REQUEST PER ASSY					COLOR	MATERIAL	DESCRIPTION	ITEM NO
A	A	A	A	REVISION OF EACH ASSY PN				
--4	--3	--2	--1	TE ASSEMBLY PN				


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN X.LI 19FEB2020		 TE Connectivity			
		CHK W.WU 02MAR2020					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		APVD LYIN 05MAR2020		NAME NTS 48P TAB HSG ASSEMBLY	
				PRODUCT SPEC 108-101662		-	
		APPLICATION SPEC		-			
MATERIAL SEE TABLE -		WEIGHT -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				A2	-	©=2366509	-
CUSTOMER DRAWING				SCALE	1:1	SHEET	1 OF 2
						REV	B1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



1	1	1	1	RUST RED	VMQ	FACIAL SEAL	5
1	-	-	-	BLUE	PBT-GF30	REAR CAP	4
-	1	-	-	GREEN			
-	-	1	-	GREY			
-	-	-	1	BLACK			
1	1	1	1	RUST RED	VMQ	GROMMET	3
1	-	-	-	BLUE	PBT-GF30	HOUSING CODING D	2
-	1	-	-	GREEN		HOUSING CODING C	
-	-	1	-	GREY		HOUSING CODING B	
-	-	-	1	BLACK		HOUSING CODING A	
1	1	1	1	YELLOW	PBT-GF30	TPA	1
QTY. REQUEST PER ASSY				COLOR	MATERIAL	DESCRIPTION	ITEM NO
A	A	A	A	REVISION OF EACH ASSY PN			
2--4	2--3	2--2	2--1	TE ASSEMBLY PN			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN X.LI 19FEB2020		 TE Connectivity			
		CHK W.WU 02MAR2020					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME NTS 48P TAB HSG ASSEMBLY			
		APVD L.YIN 05MAR2020					
		PRODUCT SPEC 108-101662					
		APPLICATION SPEC					
MATERIAL SEE TABLE		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT -		A2	-	C=2366509	-
		CUSTOMER DRAWING		SCALE 1:1		SHEET 2 OF 2	REV B1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2366509-1](#)