


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS





NOTES:

- 1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
CONTACT : COPPER ALLOY, TIN PLATED
2. ELECTRICAL
RATED CURRENT AND VOLTAGE : 20AMP 300V(UG B/C)
: 5AMP 600V(UG D)
INSULATION RESISTANCE : >2000 M Ohm (500V DC)
3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C
- 4 TOLERANCE NOT CUMULATIVE

90.62	12	1-2385012-2
83.00	11	1-2385012-1
75.38	10	1-2385012-0
67.76	9	2385012-9
60.14	8	2385012-8
52.52	7	2385012-7
44.90	6	2385012-6
37.28	5	2385012-5
29.66	4	2385012-4
22.04	3	2385012-3
14.42	2	2385012-2
DIM A	POS	TE PN



2385012-3 AS SHOWN



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24 JAN 2022 SHRICHARANA B	TE Connectivity TERMINAL BLOCK, 180 DEG HEADER, 7.62mm PITCH, TAIL LENGTH 4.5 mm		
DIMENSIONS: mm		CHK 24 JAN 2022 SUBHASREE S			
		APVD 24 JAN 2022 PRASHANTH S			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		108-32299	NAME		
		APPLICATION SPEC	SIZE		
		114-32242	CAGE CODE		
		WEIGHT	DRAWING NO		
MATERIAL		-	RESTRICTED TO		
FINISH		-	SCALE		
1		1	SHEET		
		CUSTOMER DRAWING	1 OF 1		
			REV		
			A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2385012-9](#)