



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	PRODUCTION ISSUE	29JAN2019	PNT	MT



AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS

PART NUMBER	H & J		K		P	R	S	T	HW & JW	KW
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±20%	±20%
	a	b	a	b	b	b	b	b	b	b
322A112	13.2 [.52]	5.8 [.23]	6.6 [.26]	3.0 [.12]	52.3 [2.06]	26.2 [1.03]	19.3 [.76]	N/A	1.52 [.06]	1.02 [.04]
322A123	26.9 [1.06]	12.4 [.49]	6.6 [.26]	3.0 [.12]	83.3 [3.28]	41.7 [1.64]	27.2 [1.07]	10.7 [.42]	2.54 [.10]	1.02 [.04]
322A134	26.9 [1.06]	12.7 [.50]	13.2 [.52]	5.8 [.23]	107.7 [4.24]	53.8 [2.12]	38.6 [1.52]	20.3 [.80]	2.54 [.10]	1.52 [.06]
322A148	55.6 [2.19]	25.4 [1.00]	13.2 [.52]	5.8 [.23]	180.6 [7.11]	90.4 [3.56]	57.4 [2.26]	25.4 [1.00]	4.57 [.18]	1.52 [.06]
322A158	55.6 [2.19]	25.4 [1.00]	26.9 [1.06]	12.4 [.49]	222.3 [8.75]	111.3 [4.38]	77.7 [3.06]	38.1 [1.50]	4.57 [.18]	2.54 [.10]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS:
mm [INCHES]

DWN 29JAN2019

PRAVEEN N T

CHK 29JAN2019

N NAGAR

APVD 29JAN2019

M TAYLOR

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

MATERIAL


SEE SHEET 2

FINISH

—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —
 1 PLC ± —
 2 PLC ± —
 3 PLC ± —
 4 PLC ± —
 ANGLES ± —



NAME

TRANSITION, 90 DEG. SIDE BREAKOUT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-

322A112-XX-0THRU158-XX-0

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV

T

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, Semi-Flexible ZEROHAL	RW-2082	/86;/180	S1048;S1030


ORDERING INFORMATION

The diagram illustrates the structure of a part number: **322A1XX-XX-XX/XX-0**. The components are defined as follows:

- Base part number:** 322A1XX
- Material dash number (See Compatability Chart):** -XX
- Modification number:** -XX
- Adhesive slash number (If necessary, see Compatability Chart):** /XX
- Color designator:** -0

NOTES

1. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown. On size 322A112 the vent port will be eliminated.

DIMENSIONS:		DWN	29JAN2019	MATERIAL		FINISH	
mm [INCHES]		CHK	29JAN2019	 TE Connectivity Ltd.			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	29JAN2019				
		M TAYLOR					
0 PLC ± -		PRODUCT SPEC		NAME			
1 PLC ± -		—					
2 PLC ± -		APPLICATION SPEC		TRANSITION, 90 DEG. SIDE BREAKOUT			
3 PLC ± -		—					
4 PLC ± -		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
ANGLES ± -				A4	00779	 322A112-XX-0THRU158-XX-0	—
		CUSTOMER DRAWING				SCALE	DNS
						SHEET	2 of 2
						REV	T

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[322A148-25-0](#)