


The DPT250 Cable-Extension Transducer offers a highly accurate incremental encoder output signal that can provide both position and velocity information. The output is a digital pulse stream that can provide resolution down to less than a thousandth's of an inch!

Delivering high accuracy and fine resolution without the need for perfect parallel alignment, this compact device offers the additional benefits of ease of installation and ability to interface to any PLC or controller. These features make the DPT250 the perfect choice for many applications that range from hydraulic cylinder positioning to robotic arm motion feedback.

Electrical Output Signal Options



DPT250

Cable Actuated Sensor Instrument Grade • Incremental Encoder

Short-Range String Encoder • High Resolution

25, 50-inch Stroke Range Options

Powder Painted & Anodized Aluminum Enclosure

Perfect Solution for Industrial & Testing Applications

General

Full Stroke Range Options	0-25 to 0-50 inches [0-625 to 0-1250 mm]
Output Signal	incremental encoder (quadrature)
Output Driver Options	TTL/CMOS, Open Collector, Line Driver
Accuracy	.01 to .02 in. (see ordering information)
Repeatability	.005 to .010 in. (see ordering information)
Resolution	25 to 1250 pulses per inch
Measuring Cable	0.019-in. dia. nylon-coated stainless steel
Enclosure Material	powder-painted and anodized aluminum
Sensor	optical encoder
Weight	2 lbs. max.

Electrical

Input Voltage	see ordering information
----------------------	--------------------------


Environmental

Enclosure	IP 55, NEMA 12
Operating Temperature	0°F to 160°F (-20°C to 70°C)
Vibration	up to 10g to 2000 Hz
Humidity	98% RH, no condensation


DPT250

Instrument Grade • Incremental

Outline Drawing:



Range	A
25", 625mm	1.31 [33,3]
50", 1250mm	1.63 [41,4]



ALL DIMENSIONS ARE IN INCHES [MM] • tolerances are ± 0.02 in. [$\pm 0,5$ mm]

Ordering Information

Model Number:

DPT250 - - **1** **1** - **0**
order code: **R** **A** **B** **C** **D** **E** **F** **G**

Sample Model Number:

DPT250 - 0025 - 111 - 1130

R range:	25 inches
A measuring cable tension:	standard - 12 oz.
D sensing circuit/channels:	TTL/CMOS, A,B
E resolution:	500 pulses per inch
F electrical connection:	6-pin plastic connector

Full Stroke Range:

R order code:	0025	0050	0625	1250
full stroke range, min:	25 in.	50 in.	625 mm	1250 mm
accuracy:	±0.010 in. (max)	±.020 in. (max)	±0.25 mm (max)	±0.50 mm (max)
repeatability:	±0.005 in. (max)	±.010 in. (max)	±0.12 mm (max)	±0.25 mm (max)
cable tension* (±30%):	13 oz.	6 oz.	3,6 N	1,6 N
cable acceleration, max.:	11 g	4 g	11 g	4 g
resolution options:	50, 500, 1000, 1250 pulses per inch	25, 250, 500, 625 pulses per inch	2, 20, 40, 50 pulses per mm	1, 10, 20, 25 pulses per mm

*note: increased cable tension options available (see below)

Measuring Cable Tension:

A order code:	1	H
	standard tension*	high tension*
25 inch range:	13 oz.	65 oz.
50 inch range:	6 oz.	33 oz.
625 mm range:	3,6 N	18,1 N
1250 mm range:	1,6 N	9,2 N

*—note: spring tension tolerance: ±30%

Sensing Circuit / Channels:






I order code:	1	2	4	6
description:	TTL / CMOS	open collector	line driver	universal line driver
Input voltage (V+):	4.5...13.2 Vdc	10.8...26.4 Vdc	5 Vdc	5...30 VDC
Sink current:	20 mA max.	20 mA max.	20 mA max.	20 mA max.
Input current:	80 mA max.	80 mA max.	150 mA max.	50 mA max, no load

Resolution:

B order code:	1	2	3	4
25 in. range:	500 ppi	1000 ppi	1250 ppi	50 ppi
50 in. range:	250 ppi	500 ppi	625 ppi	25 ppi
625 mm range:	20 ppmm	40 ppmm	50 ppmm	2 ppmm
1250 mm range:	10 ppmm	20 ppmm	25 ppmm	1 ppmm

Electrical Connection:

③ order code:

1			3			4		
15-inch, shielded instrumentation cable			6-pin plastic connector with mating plug			18-pin plastic connector with mating plug		
								
15-inch, multiconductor cable								
			.30 - .39 in. [8 - 10 mm] cable dia. 16 AWG max conductor size connector: MS3102E-14S-6P mating plug: MS3106E-14S-6S			.26 - .30 in. [6,6 - 7,6 mm] cable dia. 20 - 24 AWG conductor size connector: Conxall 14282-18PG-300-K mating plug: Conxall 13282-18SG-326-K		
			contact view			contact view		
	TTL/CMOS	5 V Line Driver		TTL/CMOS	5 V Line Driver		TTL/CMOS	5 V Line Driver
color	Open Collector	Universal Line Driver	pin	Open Collector	Universal Line Driver	pin	Open Collector	Universal Line Driver
red	input voltage	input voltage	A	input voltage	input voltage	1	input voltage	input voltage
black	common	common	B	common	common	2	common	common
green	channel A	channel A	C	channel A	channel A	3	channel B	channel B
white	channel B	channel B	D	channel B	channel B	6	channel A	channel A
blue	-	channel A'	E	-	channel A'	7	-	index
brown	-	channel B'	F	-	channel B'	11	-	channel B'
yellow	-	index				12	-	channel A'
orange	-	index'				15	-	index'

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity company
20630 Plummer Street
Chatsworth, CA 91311
Tel +1 800 423 5483
Tel +1 818 701 2750
Fax +1 818 701 2799
customercare@chtw@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

DPT250 12/01/2015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[04-0953-0029](#)