







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

AMP WIRE RANGE	 LR7189 Certified
SEE TABLE STRANDED	WIRE SIZE PER TABLE STRANDED



- 1 STAMP AMP  APPROX AS SHOWN
SEE TABLE BELOW.
- 2 WIRE INSULATION DIA: 0.965–2.794[.038–.110] FOR 22 AWG
1.168–2.794[.046–.110] FOR 20 AWG
1.422–2.794[.056–.110] FOR 18 AWG
- 3 BODY MATERIAL THK: 0.787±0.051[.031±.002].
- 4 APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE.
- 5 CSA CERTIFIED

5	M7928/1-37 CLASS 1	WHITE	18*	18	1000	LOOSE PIECE	2-328975-3	
5	M7928/1-28 CLASS 1	RED	20*	20	1000	LOOSE PIECE	2-328975-2	
5	M7928/1-19 CLASS 1	GREEN	22*	22	1000	LOOSE PIECE	2-328975-1	
	MILITARY P/N AND CLASS	STRIPE COLOR	1	STAMPING	WIRE SIZE	QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE: 105°C[221°F] MAX

VOLTAGE RATING: 300 V MAX

WIRE RANGE:

CIRC MIL AREA

22 0.38mm² [754]


20 0.60mm² [1,186]

18 0.96mm² [1,900]

STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



MATERIAL
BODY & SLEEVE
COPPER PER ASTM B-152
INSULATION: NYLON

FINISH

BODY & SLEEVE
TIN PLATE
PER ASTM B545
INSULATION: COLOR-RED

DWN DK SCHRUM 9/8/93

CHK RE HERSEY 9/8/93

APVD ML ELLIS 9/8/93

PRODUCT SPEC

APPLICATION SPEC

114-2157

WEIGHT -

CUSTOMER DRAWING

 TE Connectivity Ltd.

NAME
TERMINAL, RING TONGUE, PIDG™,
WIRE SIZE, 22, 20 & 18 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-328975

SCALE NTS

SHEET 2 OF 2

REV P2

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-328975-3](#)