







PCB THICKNESS: 1.6±0.1



	NIL	NIL	14	7	16	16	5-		-3
	NIL	NIL	38	19	40	40	5-		-2
	5, 16		14	7	16	16	5-		-1
	3, 16		14	7	16	16	5-		-0
	1, 8		6	3	8	8	4-		-9
	NIL		48	24	50	50	4-		-8
			46	23	48	48	4-		-7
			44	22	46	46	4-		-6
			40	20	42	42	4-		-4
			36	18	38	38	4-		-2
			34	17	36	36	4-		-1
			32	16	34	34	4-		-0
			30	15	32	32	3-		-9
			26	13	28	28	3-		-7
			20	10	22	22	3-		-4
			18	9	20	20	3-		-3
			16	8	18	18	3-		-2
			12	6	14	14	3-		-0
			4	2	6	6	2-		-6
		0, 76 μ m	2	1	4	4	2-		-5
			48	24	50	50	2-		-4
			46	23	48	48	2-		-3
			44	22	46	46	2-		-2
			42	21	44	44	2-		-1
			40	20	42	42	2-		-0
			38	19	40	40	1-		-9
			36	18	38	38	1-		-8
			30	15	32	32	1-		-5
			28	14	30	30	1-		-4
			24	12	26	26	1-		-2
			16	8	18	18			-8
			14	7	16	16			-7
			12	6	14	14			-6
			10	5	12	12			-5
			8	4	10	10			-4
			6	3	8	8			-3
		0, 2 μ m	2	1	4	4	5176837-1		

FINISH	PIN OMITTED	"D"	"C"	"B" SPACES	"A" REF	NO OF POS	ASS'Y P/N
--------	----------------	-----	-----	---------------	------------	--------------	--------------

		DWN WYLEE 07MAR2005		 TE Connectivity	
		CHK VINCENT TAN			
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
mm				AMPMODU 2mm PITCH POST HDR, HORIZONTAL TYPE, L=2.6	
		0 PLC ±0.25		APVD	
		1 PLC ±0.2		SE LFONG	
		2 PLC ±0.2		PRODUCT SPEC	
		3 PLC ±		-	
		4 PLC ±		APPLICATION SPEC	
GENERAL TOLERANCE		ANGLES ±		SIZE	
0<+ 10 : ±0.2				CAGE CODE	
10<+ 30 : ±0.25				DRAWING NO	
30<+ 100 : ±0.3				A2 00779	
ANGLES : ±3°				C=5176837	
MATERIAL		FINISH		WEIGHT	
		 		-	
				CUSTOMER DRAWING	
				SCALE - SHEET 1 OF 1 REV S	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-5176837-7](#)