



$$0.89 \pm [0.035 \pm 0.003]$$


	$\phi 0.15$	$[.006]$	(S)
---	-------------	----------	-----

TYP



- | | | | | | | |
|---------------|---------------|---------------|---------------|--------------|----|---------------|
| 4206-5 | $\triangle_2$ | 99.06[3.900] | 101.60[4.000] | 80 | | 4-534206-0 |
| | $\triangle_2$ | 96.52[3.800] | 99.06[3.900] | 78 | | 3-534206-9 |
| | $\triangle_2$ | 93.98[3.700] | 96.52[3.800] | 76 | | 3-534206-8 |
| | $\triangle_2$ | 91.44[3.600] | 93.98[3.700] | 74 | | 3-534206-7 |
| | $\triangle_2$ | 88.90[3.500] | 91.44[3.600] | 72 | | 3-534206-6 |
| | $\triangle_2$ | 86.36[3.400] | 88.90[3.500] | 70 | | 3-534206-5 |
| | $\triangle_2$ | 83.82[3.300] | 86.36[3.400] | 68 | | 3-534206-4 |
| | $\triangle_2$ | 81.28[3.200] | 83.82[3.300] | 66 | | 3-534206-3 |
| | $\triangle_2$ | 78.74[3.100] | 81.28[3.200] | 64 | | 3-534206-2 |
| | $\triangle_2$ | 76.20[3.000] | 78.74[3.100] | 62 | | 3-534206-1 |
| | $\triangle_2$ | 73.66[2.900] | 76.20[3.000] | 60 | | 3-534206-0 |
| | $\triangle_2$ | 71.12[2.800] | 73.66[2.900] | 58 | | 2-534206-9 |
| | $\triangle_2$ | 68.58[2.700] | 71.12[2.800] | 56 | | 2-534206-8 |
| | $\triangle_2$ | 66.04[2.600] | 68.58[2.700] | 54 | | 2-534206-7 |
| | $\triangle_2$ | 63.50[2.500] | 66.04[2.600] | 52 | | 2-534206-6 |
| | 4206-1 | $\triangle_2$ | 60.96[2.400] | 63.50[2.500] | 50 | |
| $\triangle_2$ | | 58.42[2.300] | 60.96[2.400] | 48 | | 2-534206-4 |
| $\triangle_2$ | | 55.88[2.200] | 58.42[2.300] | 46 | | 2-534206-3 |
| $\triangle_2$ | | 53.34[2.100] | 55.88[2.200] | 44 | | 2-534206-2 |
| $\triangle_2$ | | 50.80[2.000] | 53.34[2.100] | 42 | | 2-534206-1 |
| $\triangle_2$ | | 48.26[1.900] | 50.80[2.000] | 40 | | 2-534206-0 |
| $\triangle_2$ | | 45.72[1.800] | 48.26[1.900] | 38 | | 1-534206-9 |
| $\triangle_2$ | | 43.18[1.700] | 45.72[1.800] | 36 | | 1-534206-8 |
| $\triangle_2$ | | 40.64[1.600] | 43.18[1.700] | 34 | | 1-534206-7 |
| $\triangle_2$ | | 38.10[1.500] | 40.64[1.600] | 32 | | 1-534206-6 |
| $\triangle_2$ | | 35.56[1.400] | 38.10[1.500] | 30 | | 1-534206-5 |
| $\triangle_2$ | | 33.02[1.300] | 35.56[1.400] | 28 | | 1-534206-4 |
| $\triangle_2$ | | 30.48[1.200] | 33.02[1.300] | 26 | | 1-534206-3 |
| $\triangle_2$ | | 27.94[1.100] | 30.48[1.200] | 24 | | 1-534206-2 |
| $\triangle_2$ | | 25.40[1.000] | 27.94[1.100] | 22 | | 1-534206-1 |
| | | $\triangle_2$ | 22.86[.900] | 25.40[1.000] | 20 | |
| | $\triangle_2$ | 20.32[.800] | 22.86[.900] | 18 | | 534206-9 |
| | $\triangle_2$ | 17.78[.700] | 20.32[.800] | 16 | | 534206-8 |
| | $\triangle_2$ | 15.24[.600] | 17.78[.700] | 14 | | 534206-7 |
| | $\triangle_2$ | 12.70[.500] | 15.24[.600] | 12 | | 534206-6 |
| | $\triangle_8$ | 10.16[.400] | 12.70[.500] | 10 | | 534206-5 |
| | $\triangle_8$ | 7.62[.300] | 10.16[.400] | 8 | | 534206-4 |
| | $\triangle_8$ | 5.08[.200] | 7.62[.300] | 6 | | 534206-3 |
| | $\triangle_8$ | 2.54[.100] | 5.08[.200] | 4 | | 534206-2 |
| | 9 | $\triangle_2$ | - | 2.54[.100] | 2 | $\triangle_6$ |

FINISH	B	A	NO. OF .POSN	PART NUMBER
--------	---	---	-----------------	----------------



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN M.BINNER 06NOV2002 CHK 06NOV02 J.OLSON APVD 06NOV02		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD II, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU		
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -				
MATERIAL		FINISH				
						
		WEIGHT		SIZE A2		
				CAGE CODE 00779		DRAWING NO C-534206
				RESTRICTED TO —		
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 2
						REV R7

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

9	1.1	99.06[3.900]	101.60[4.000]	80	12	9-534206-0
	1.1	96.52[3.800]	99.06[3.900]	78	12	8-534206-9
	1.1	93.98[3.700]	96.52[3.800]	76	12	8-534206-8
	1.1	91.44[3.600]	93.98[3.700]	74	12	8-534206-7
	1.1	88.90[3.500]	91.44[3.600]	72	12	8-534206-6
	1.1	86.36[3.400]	88.90[3.500]	70	12	8-534206-5
	1.1	83.82[3.300]	86.36[3.400]	68	12	8-534206-4
	1.1	81.28[3.200]	83.82[3.300]	66	12	8-534206-3
	1.1	78.74[3.100]	81.28[3.200]	64	12	8-534206-2
	1.1	76.20[3.000]	78.74[3.100]	62	12	8-534206-1
	1.1	73.66[2.900]	76.20[3.000]	60	12	8-534206-0
	1.1	71.12[2.800]	73.66[2.900]	58	12	7-534206-9
	1.1	68.58[2.700]	71.12[2.800]	56	12	7-534206-8
	1.1	66.04[2.600]	68.58[2.700]	54	12	7-534206-7
	1.1	63.50[2.500]	66.04[2.600]	52	12	7-534206-6
	1.1	60.96[2.400]	63.50[2.500]	50	12	7-534206-5
	1.1	58.42[2.300]	60.96[2.400]	48	12	7-534206-4
	1.1	55.88[2.200]	58.42[2.300]	46	12	7-534206-3
	1.1	53.34[2.100]	55.88[2.200]	44	12	7-534206-2
	1.1	50.80[2.000]	53.34[2.100]	42	12	7-534206-1
	1.1	48.26[1.900]	50.80[2.000]	40	12	7-534206-0
	1.1	45.72[1.800]	48.26[1.900]	38	12	6-534206-9
	1.1	43.18[1.700]	45.72[1.800]	36	12	6-534206-8
	1.1	40.64[1.600]	43.18[1.700]	34	12	6-534206-7
	1.1	38.10[1.500]	40.64[1.600]	32	12	6-534206-6
	1.1	35.56[1.400]	38.10[1.500]	30	12	6-534206-5
	1.1	33.02[1.300]	35.56[1.400]	28	12	6-534206-4
	1.1	30.48[1.200]	33.02[1.300]	26	12	6-534206-3
	1.1	27.94[1.100]	30.48[1.200]	24	12	6-534206-2
	1.1	25.40[1.000]	27.94[1.100]	22	12	6-534206-1
	1.1	22.86[.900]	25.40[1.000]	20	12	6-534206-0
	1.1	20.32[.800]	22.86[.900]	18	12	5-534206-9
1.1	17.78[.700]	20.32[.800]	16	12	5-534206-8	
1.1	15.24[.600]	17.78[.700]	14	12	5-534206-7	
1.1	12.70[.500]	15.24[.600]	12	12	5-534206-6	
9	1.1	10.16[.400]	12.70[.500]	10	12	5-534206-5
9	1.1	7.62[.300]	10.16[.400]	8	12	5-534206-4
9	1.1	5.08[.200]	7.62[.300]	6	12	5-534206-3
9	1.1	2.54[.100]	5.08[.200]	4	12	5-534206-2
9	1.1	-	2.54[.100]	2	6/12	5-534206-1

FINISH	B	A	NO OF POSN	PART NUMBER
--------	---	---	---------------	----------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002 CHK J.OLSON 06NOV02 APVD J.OLSON 06NOV02		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD II, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -			
MATERIAL		FINISH			
					
		WEIGHT -		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C=534206	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1	
				SHEET 2 of 2	
				REV R7	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[534206-6](#)