



# Wi-Fi 6/6E TRIPLE BAND EMBEDDED ANTENNA

**Part Numbers:** 2344657-1, 2344657-2  
2344657-3, 2344657-4  
2344657-5, 2344657-6  
2344657-7, 2344657-8  
2344657-9

## FEATURES & BENEFITS


- Wi-Fi 6, also including Wi-Fi 6E new 6GHz band, Bluetooth, ZigBee
- Adhesive backing on FPC simplifies mounting within the device
- Omnidirectional coverage
- No matching components required
- Ground-plane independent design
- Different cable length and connector options available

## SPECIFICATIONS (Shown as 2344657-1 : Others can vary with different cable lengths.)


Frequency Range (MHz)	2400-2500	5150-5875	5925-7125
VSWR	< 2.7:1	< 2.1:1	< 2.1:1
Average Efficiency	61%	72%	66%
Peak Gain	1.1dBi	4.9dBi	5.3dBi
Average Gain	-2.5dB	-1.1dB	-1.4dB
Power Handling	10 Watt cw		
Feed Point Impedance	50 ohms unbalanced		
Polarization	Linear		
Size	35 mm x 8.0 mm x 0.2 mm		
Weight	< 0.8 g		
Mounting	Adhesive Tape		
Mating Connectors	MHF and MHF4-type, Refer to page 5		
Cable (Coaxial)	0.81mm and 1.13mm Dia., Refer to page 5		
Operating Temperature	-40 to +85°C		
Storage Temperature	-40 to +85°C		
Hazardous Materials	A certificate of conformance is available from the product page on TE website.		

RF DATA (Shown as 2344657-1 : Others can vary with different cable lengths.)


VSWR



Return Loss




Efficiency



Data measured in free space and on plastic device enclosure


# RADIATION PATTERN

(Shown as 2344657-1 : Others can vary with different cable lengths.)




Data measured in free space and on plastic device enclosure

KEEP OUT AREA




- NOTES**
- 1. Antenna designed to be mounted on plastic cover.
  - 2. Area in blue indicates Keep Out Area
  - 3. Contact TE if keep out zone cannot be guaranteed.



Dimension: mm  
Diagrams is not into scale

DIMENSIONS  
(Refer to Page5 for dimension “A” and “B”)



Dimension: mm  
Diagrams is not into scale


MATING COMPONENTS TO PART NUMBERS AND DIMENSIONS

2344657-1	50	1.97	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-2	100	3.94	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-3	150	5.91	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-4	200	7.87	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-9	250	9.84	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-5	50	1.97	0.81	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344657-6	100	3.94	0.81	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344657-7	150	5.91	0.81	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344657-8	200	7.87	0.81	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
PART NUMBER	MM	INCH	CABLE O.D(B), MM	CONNECTOR TYPE (ON CABLE)	PART NUMBER	IMAGE
CABLE LENGTH ("A")		MATING COMPONENTS				


PACKAGING



50PCS/BUNCH



200PCS/BAG  
DESICCANT: 1 PCS/BAG



TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752  
Canada: +1 (905) 475-6222  
Mexico: +52 (0) 55-1106-0800  
Latin/S. America: +54 (0) 11-4733-2200  
Germany: +49 (0) 6251-133-1999  
UK: +44 (0) 800-267666  
France: +33 (0) 1-3420-8686  
Netherlands: +31 (0) 73-6246-999  
China: +86 (0) 400-820-6015  
For phone numbers in other countries, go to [te.com/support-center](https://te.com/support-center)

te.com

TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.

12/2021

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2344657-2](#)