

# SPECIFICATION CONTROL DRAWING

55A4141

TITLE FOUR CONDUCTOR CABLE, JACKETED, GENERAL PURPOSE, 600 VOLT

Date 11-18-10 Revision B

This specification sheet forms a part of the latest issue of Raychem Specification 55A.



CABLE CONSTRUCTION DETAILS						
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
		MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A4141-30-*	30	.006	.008	.074	.086	4.2
55A4141-28-*	28	.006	.008	.081	.095	5.4
55A4141-26-*	26	.006	.008	.093	.109	7.6
55A4141-24-*	24	.006	.008	.106	.124	10.4
55A4141-22-*	22	.006	.008	.120	.141	13.9
55A4141-20-*	20	.006	.008	.137	.161	20.4
55A4141-18-*	18	.006	.008	.161	.190	30.0
55A4141-16-*	16	.006	.008	.181	.213	37.7
55A4141-14-*	14	.007	.009	.224	.264	58.5
55A4141-12-*	12	.007	.009	.267	.316	86.9
55A4141-10-*	10	.008	.010	.330	.391	139.

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

### TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

### VOLTAGE RATING: 600 volts (rms) at sea level

### ACCELERATED AGING: 300 ± 3°C for 7 hours

### BLOCKING: 200 ± 3°C for 6 hours

### DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

### FLAMMABILITY (Procedure 1): 3 seconds (maximum);

3 in. (maximum); no flaming of facial tissue

### JACKET COLOR: White preferred

### JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)

### LIFE CYCLE: 200 ± 3°C for 168 hours

### LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

### PART NUMBER:

The "\*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

1/ Example: AWG 20, black, brown, red and orange component wires; white jacket: 55A4141-20-0/1/2/3-9

NOTE: Nominal values are for information only.  
Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.  
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1	The TE logo, Tyco Electronics and Raychem are trademarks.	Tyco Electronics	Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.		
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55A4141-22-MST4-9CS2275](#)