

COIL: @ 25°C

RESISTANCE 50 OHMS \pm 10%

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE VOLTAGE 2.7 VDC

TURN-ON BASE CURRENT 0.75 mADC

MUST RELEASE 1.4 VDC MAX, 0.22 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: TURN-ON TIME 2.0 MS MAX

TURN-OFF TIME 7.5 MS MAX

CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/24/98 *CK* *VERBY* 3/24/98

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. QPL
CUST. NO. M28776/1-025M

TYPE "JMAT" RELAY

JMACT-5XM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMACT-5XM](#)