





REV. 0
DCO 143342

COIL: @ 25°C
 RESISTANCE 39 OHMS ± 10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 3.2 VDC
 MUST RELEASE 2.3 VDC MAX, 0.6 VDC MIN

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C
 NOTES: OPERATE TIME 2.0 MS MAX.
RELEASE TIME 4.0 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 12/03/01

CK. *[Signature]* 12/3/01

CII Technologies
 advanced control electronic solutions

CUST. QPL
 CUST. NO. M39016/20-037L REV.

"JMADD" RELAY

JMAPDD-5XL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMAPDD-5XL](#)